



Main

Range of product	Harmony 9001K
Product or component type	Contact block with protected terminals
Component name	9001K
Contacts type and composition	1 NC
Contacts operation	Standard
Connections - terminals	Screw clamp terminals , 1 x 0.22...2 x 1.5 mm ² conforming to IEC 60947-1

Complementary

Tightening torque	0.8 N.m cross slotted screw head conforming to IEC 60947-1
[Ie] rated operational current	0.55 A at 125 V DC-13 , A600-Q600 3 A at 240 V AC-15 , A600-Q600
[Ui] rated insulation voltage	250 V pollution degree 3 conforming to IEC 60947-1
[Uimp] rated impulse withstand voltage	2.5 kV conforming to IEC 60947-1
Contacts material	Silver alloy contacts
Positive opening	With conforming to IEC 60947-5-2
Short circuit protection	10 A cartridge fuse protection conforming to IEC 60947-5-1
[Ith] conventional free air thermal current	10 A
[Icm] rated short-circuit making capacity	≤ 0.1 kA at 600 V DC-13 ≤ 0.27 kA at 250 V DC-13 ≤ 0.55 kA at 125 V DC-13 ≤ 12 kA at 600 V AC-15 , 7200 VA ≤ 15 kA at 480 V AC-15 , 7200 VA ≤ 30 kA at 240 V AC-15 , 7200 VA ≤ 60 kA at 120 V AC-15 , 7200 VA
Rated breaking capacity	≤ 0.1 kA at 600 V DC-13 ≤ 0.27 kA at 250 V DC-13 ≤ 0.55 kA at 125 V DC-13 ≤ 1.2 kA at 600 V AC-15 , 720 VA ≤ 1.5 kA at 480 V AC-15 , 720 VA ≤ 3 kA at 240 V AC-15 , 720 VA ≤ 6 kA at 120 V AC-15 , 720 VA
Product weight	0.023 kg

Environment

Standards	CSA C22-2 No 14 EN/IEC 60947-5-1 IEC 60947-1 IEC 60947-5-4 JIS C 4520 JIS C 852 UL 508
Protective treatment	TC
Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...70 °C
Vibration resistance	7 gn (f = 2...500 Hz) conforming to IEC 60068-2-6
Shock resistance	50 gn conforming to IEC 60068-2-27
Class of protection against electric shock	Class II conforming to IEC 60536
IP degree of protection	IP20 conforming to NF C 20-010 IP20 conforming to IEC 60529

RoHS EUR status	Will be compliant
RoHS EUR conformity date	2Q2009
