



Stealth Cutters

Strong, versatile and long-lasting

CUTTING PERFORMANCE... Lowest Cost per Cut

- Hundreds of thousands of cuts are possible before edges become dull
- Cutting fine wire or leads equal to or thinner than the width of a human hair
- Carbon steel construction - hardness of C63-65 (Rockwell Scale)
- Individually hand-tested hardened blades

COMFORT

- Ergonomically designed ESD Safe Grips for exceptional comfort
- Dual leaf springs for ease of use

Head Shape



Oval

The most popular shape can be used for many applications. Designed to be durable. Options: regular and large oval head; with semi-flush or flush cutting.

Cutting Edges



Semi-Flush

Cutting edges have a slight bevel, which produces cuts with a small pinch on the tip of the cut wire. Longest cutting life.



Flush

Cutting edges have a minimum bevel, which produces cuts with a very small pinch.

Order #	Description
10921F	Oval Head - Flush Cutting Capacity: 0.15 to 1.15mm*
10921S	Oval Head - Semi-Flush Cutting Capacity: 0.2 to 1.2mm*
10922F	Large Oval Head - Flush Cutting Capacity: 0.15 to 1.20mm*
10922S	Large Oval Head - Semi-Flush Cutting Capacity: 0.20 to 1.50mm*

*Cutting Capacity: Diameter of Soft Copper wire