

High-Efficiency Beveled Tip (#7579-100)

Diameter is 3/32" or .094".

Note: High-Efficiency tips heat up faster and provide more than 20% more soldering time than our standard tips.

High-Efficiency tips reach soldering temperature in less than 10 seconds and reach a tip temperature of approximately 900°F.