

The world's toughest keyboard has been cut down to size...

Storm 2210-T/B

Compact format, vandal resistant, keyboard with integrated tracker ball

- 63 Keys
- A water and impact resistant tracker ball make this keyboard the complete and ideal solution for PC data entry in menu based "point and click" applications
- Tough, vandal resistant construction
- Compact format: 360.0 x 117.6 x 38.5mm
- Integral 38mm, PS2 compatible tracker ball with left and right click keys.

All STORM keyboards are:

IP65 specification seal against water & dust

Operational range -20°C (dry) to +75°C

Integral PS2/USB interface electronics (switchable)

Optional PC connection cables (sold separately)

Optional fixing kit for under panel installation (sold separately)

RFI / EMI Protection in accordance with current and forthcoming European and US directive

Operational life of more than 4 million cycles per key

Resistant to most corrosives and cleaning agents

Vandal Resistant Metal Key Version:
Brushed stainless steel with cast metal keys

Case colour:
Black

Keytop colour:
Silver chrome with permanently engraved keytop characters in black

Vandal Resistant Version:
Brushed stainless steel with high impact polymer keys

Case colour:
Black

Keytop colour:
Black molded polymer with permanent laser engraved keytop characters in white

Storm 2210

Compact format, vandal resistant, keyboard

- 61 Keys
- Compact format: 290.0 x 117.6 x 38.5mm.

Storm 2220

Compact format, vandal resistant, keyboard with extra function keys

- 75 Keys
- Compact format: 290.0 x 137 x 38.5mm with additional function keys along the top row.

Storm 2230

Fully featured, vandal resistant, keyboard with numeric/arithmetic function keypad

- 93 Keys
- Space efficient footprint 346mm x 137mm x 38.5mm
- Non embedded numeric/arithmetic keypad.

Storm 1200

Vandal resistant sub-miniature keyboard

Developed for use in a new generation of data entry terminals, this miniature but highly responsive keyboard is suitable for use in hostile environments, where panel space is at a premium. Its robust construction is highly resistant to hard use, abuse and vandalism. It is sealed against water and dust to ensure responsive and reliable data entry in the most demanding situations. Integral interface electronics provide a compatible, ready to use solution for most PC based applications.

- 53 Keys
- Very small footprint: 175mm x 85mm x 21.5 mm
- Stainless steel front plate and silver chromed metal keys.

... **Storm** keyboards are smaller, tougher and even better value.

STORM keyboards are constructed to survive in exposed, unsupervised, public environments. Their responsive key action ensures rapid, reliable and responsive data entry in tough, wet or industrial conditions. A hardened stainless steel front plate and captive, cast metal or high impact polymer keys ensure the keyboard's resistance to hard use, abuse and vandalism.



FM 39602



Whilst every effort is made to ensure details are correct at time of print, specifications are subject to change without notice.

K.EX-doc - Jan 01

www.keymat.com

Storm Data Entry Technology
364 Pennsylvania Avenue, Suite 202
Glen Ellyn, Illinois, 60137, USA
Tel: 630 469 2981
Fax: 630 469 2975

Email: sales.usa@storm-keypads.com

Storm
data entry technology

Keymat Technology
14 Bentinck Court, Bentinck Road
West Drayton, Middlesex UB7 7RQ UK
Tel: +44 (0)1895 431421
Fax: +44 (0)1895 431132
Email: sales@keymat.com