

8919 Hook-up/Lead - UL AWM Style 1015

For more Information
please call

1-800-Belden1



Description:

Tinned copper conductor, PVC insulation. Rated 105°C, 600V. Rated 2500V peak for electronic circuits, and internal wiring of electronic and electrical equipment.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
1	20	10x30	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	.030

Overall Insulation

Overall Cable

Overall Nominal Diameter: 0.100 in.

Mechanical Characteristics (Overall)

Bulk Cable Weight: 7.500 lbs/1000 ft.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

UL Rating:	600 V, 105°C
UL Type:	MTW or AWM 1015/1230
CSA Rating:	600 V, 105°C
CSA Type:	AWM I A/B or TEW
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	VW-1
CSA Flame Test:	FT1

Plenum/Non-Plenum

Plenum (Y/N): No

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8919 0011000	1,000 FT	8.000 LB	BROWN	P	20 STR PVC BRN
8919 002100	100 FT	0.900 LB	RED		20 STR PVC RED
8919 0021000	1,000 FT	8.000 LB	RED	P	20 STR PVC RED
8919 0031000	1,000 FT	8.000 LB	ORANGE	P	20 STR PVC ORG
8919 004100	100 FT	0.900 LB	YELLOW		20 STR PVC YEL
8919 0041000	1,000 FT	8.000 LB	YELLOW	P	20 STR PVC YEL
8919 005100	100 FT	0.900 LB	GREEN, DARK		20 STR PVC GRN
8919 0051000	1,000 FT	8.000 LB	GREEN, DARK	P	20 STR PVC GRN
8919 0081000	1,000 FT	8.000 LB	GRAY	P	#20 STR PVC GRY
8919 009100	100 FT	0.900 LB	WHITE		20 STR PVC WHT
8919 0091000	1,000 FT	858.000 LB	WHITE	P	20 STR PVC WHT
8919 010100	100 FT	0.900 LB	BLACK		20 STR PVC BLK
8919 0101000	1,000 FT	858.000 LB	BLACK	P	20 STR PVC BLK
8919 0105000	5,000 FT	40.000 LB	BLACK	C	#20 STR PVC BLK
8919 013100	100 FT	0.900 LB	BLUE, DARK		20 STR PVC DK.BLU
8919 0131000	1,000 FT	8.000 LB	BLUE, DARK	P	20 STR PVC DK.BLU
8919 0135000	5,000 FT	40.000 LB	BLUE, DARK	P	20 STR PVC DBLU

Notes:

C = CRATE REEL PUT-UP.

P = STRIPE COLORS ON STOCK SOLID COLORS. STRIPING ADDER OF \$8.00/M' FOR 1 OR 2 STRIPES. 10000' MINIMUM ORDER FOR COLOR COMBINATION.PUT-UP WILL BE SUBJECT TO TWO PIECES (+ OR -) 10% PER SPOOL

Revision Number: 2 Revision Date: 08-26-2008

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.