

AC TO AC ADAPTOR

Ideal Power Ltd.

77DB-10-15M

INPUT VOLTAGE	240VAC
OUTPUT VOLTAGE	15VAC

ELECTRICAL & MECHANICAL SPECIFICATION



KM81689



1 8 7 1 8




ELECTRONICAL SPECIFICATION



Input Voltage	240	Volts
Frequency (Hz)	50	Hz
Power Rated (W)	14.6	W
Exciting Current With No load	70	mA Max
Exciting Current With Full load	100	mA Max
Output Voltage	15	Volts+5%
Output Current	0.67	Amp
Output Voltage Without Load	18.8	Volts±5%

HI-POT :

Test Time	1	Min
PRI TO SEC	3750	Volts
PRI TO CORE	3750	Volts
SEC TO CORE	1250	Volts
Efficiency	80	%
Insulation Class	B (130)	°C



OUTPUT CORD:
2468 22AWG*2C 80°C




MECHANICAL SPECIFICATION

Dimensions (L*W*H)	81.5*56.5*48.5	mm
Weight		g
Environment:		
Operating Temperature	-10 To 40	°C
Storage Temperature	-20 To 70	°C
Relative Temperature 40°C±2°C		
RELATIVE HUMIDITY	90% RH	

Input Cable: **BS PLUG IN**

Output Cable: **2468 22AWG/2C 80 °C 1.8M LENGTH+JACK**

ELECTRICAL CIRCUIT



Head Office : Acorn House, Tree Beech Enterprise Park, Gunn, Barnstaple, Devon, England EX32 7NZ

TEL: +44 (0) 845 260 3400

FAX: +44 (0) 845 260 3400

E-Mail: info@idealpower.co.uk

WEB: www.idealpower.co.uk