

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [35151-0214](#)
Status: **Active**
Overview: [VersaBlade™](#)
Description: 6.20mm Pitch Wire-to-Wire VersaBlade™ Hybrid Receptacle Housing, 2 Circuits, Polyester UL94V-0, Blue

Documents:

3D Model	Product Specification PS-35524-001 (PDF)
Drawing (PDF)	Packaging Specification PK-35151-003 (PDF)
Product Specification PS-35150-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
TUV	R72090206
UL	E29179

General

Product Family	Crimp Housings
Series	35151
Application	Power, Wire-to-Wire
Comments	Polarized to Mating Part, Positive Lock
Overview	VersaBlade™
Product Name	VersaBlade™

Physical

Circuits (maximum)	2
Color - Resin	Blue
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.20mm
Pitch - Termination Interface	6.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +120°C

Material Info

UPC	800753526822
-----	--------------

Reference - Drawing Numbers

Packaging Specification	PK-35151-003
Product Specification	PS-35150-001, PS-35524-001
Sales Drawing	SD-35151-021*




image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[35151Series](#)

Mates With

[35150021*](#) Plug Housings

Use With

[35746](#) VersaBlade™ Crimp Terminals