

2.5V Drive Nch+Nch MOS FET

EM6K1

●Structure

Silicon N-channel MOS FET

●Features

- 1) Two 2SK3019 transistors in a single EMT package.
- 2) The MOS FET elements are independent, eliminating mutual interference.
- 3) Mounting cost and area can be cut in half.
- 4) Low on-resistance.
- 5) Low voltage drive (2.5V) makes this device ideal for portable equipment.

●Applications

Interfacing, switching (30V, 100mA)

●Packaging specifications

Type	Package	Taping
	Code	T2R
	Basic ordering unit (pieces)	8000
EM6K1		○

●Absolute maximum ratings (Ta=25°C)


<It is the same ratings for Tr1 and Tr2.>

Parameter	Symbol	Limits	Unit
Drain-source voltage	V_{DSS}	30	V
Gate-source voltage	V_{GSS}	± 20	V
Drain current	Continuous	I_D	± 100 mA
	Pulsed	I_{DP}^{*1}	± 400 mA
Total power dissipation	P_D^{*2}	150	mW / TOTAL
		120	mW / ELEMENT
Channel temperature	T_{ch}	150	°C
Storage temperature	T_{stg}	-55 to +150	°C


*1 $P_w \leq 10 \mu s$, Duty cycles $\leq 1\%$

*2 With each pin mounted on the recommended lands.

●External dimensions (Unit : mm)



●Equivalent circuit



* A protection diode has been built in between the gate and the source to protect against static electricity when the product is in use. Use the protection circuit when rated voltages are exceeded.

Transistor

●Electrical characteristics (Ta=25°C)

<It is the same characteristics for Tr1 and Tr2.>

Parameter	Symbol	Min.	Typ.	Max.	Unit	Conditions
Gate-source leakage	I_{GSS}	–	–	± 1	μA	$V_{GS}=\pm 20V, V_{DS}=0V$
Drain-source breakdown voltage	$V_{(BR)DSS}$	30	–	–	V	$I_D=10\mu A, V_{GS}=0V$
Zero gate voltage drain current	I_{DSS}	–	–	1.0	μA	$V_{DS}=30V, V_{GS}=0V$
Gate threshold voltage	$V_{GS(th)}$	0.8	–	1.5	V	$V_{DS}=3V, I_D=100\mu A$
Static drain-source on-state resistance	$R_{DS(on)}$	–	5	8	Ω	$I_D=10mA, V_{GS}=4V$
	$R_{DS(on)}$	–	7	13	Ω	$I_D=1mA, V_{GS}=2.5V$
Forward transfer admittance	$ Y_{fs} $	20	–	–	mS	$V_{DS}=3V, I_D=10mA$
Input capacitance	C_{iss}	–	13	–	pF	$V_{DS}=5V$
Output capacitance	C_{oss}	–	9	–	pF	$V_{GS}=0V$
Reverse transfer capacitance	C_{rss}	–	4	–	pF	$f=1MHz$
Turn-on delay time	$t_{d(on)}$	–	15	–	ns	$I_D=10mA, V_{DD}=5V$
Rise time	t_r	–	35	–	ns	$V_{GS}=5V$
Turn-off delay time	$t_{d(off)}$	–	80	–	ns	$R_L=500\Omega$
Fall time	t_f	–	80	–	ns	$R_G=10\Omega$

●Electrical characteristic curves




Fig.1 Typical Output Characteristics




Fig.2 Typical Transfer Characteristics




Fig.3 Gate Threshold Voltage vs. Channel Temperature




Fig.4 Static Drain-Source On-State Resistance vs. Drain Current (I)




Fig.5 Static Drain-Source On-State Resistance vs. Drain Current (II)




Fig.6 Static Drain-Source On-State Resistance vs. Gate-Source Voltage

Transistor




Fig.7 Static Drain-Source On-State Resistance vs. Channel Temperature




Fig.8 Forward Transfer Admittance vs. Drain Current




Fig.9 Reverse Drain Current vs. Source-Drain Voltage (I)




Fig.10 Reverse Drain Current vs. Source-Drain Voltage (II)




Fig.11 Typical Capacitance vs. Drain-Source Voltage




Fig.12 Switching Characteristics

●Switching characteristics measurement circuits




Fig.13 Switching Time Test Circuit




Fig.14 Switching Time Waveforms

Notes

- No technical content pages of this document may be reproduced in any form or transmitted by any means without prior permission of ROHM CO.,LTD.
- The contents described herein are subject to change without notice. The specifications for the product described in this document are for reference only. Upon actual use, therefore, please request that specifications to be separately delivered.
- Application circuit diagrams and circuit constants contained herein are shown as examples of standard use and operation. Please pay careful attention to the peripheral conditions when designing circuits and deciding upon circuit constants in the set.
- Any data, including, but not limited to application circuit diagrams information, described herein are intended only as illustrations of such devices and not as the specifications for such devices. ROHM CO.,LTD. disclaims any warranty that any use of such devices shall be free from infringement of any third party's intellectual property rights or other proprietary rights, and further, assumes no liability of whatsoever nature in the event of any such infringement, or arising from or connected with or related to the use of such devices.
- Upon the sale of any such devices, other than for buyer's right to use such devices itself, resell or otherwise dispose of the same, no express or implied right or license to practice or commercially exploit any intellectual property rights or other proprietary rights owned or controlled by
- ROHM CO., LTD. is granted to any such buyer.
- Products listed in this document are no antiradiation design.

The products listed in this document are designed to be used with ordinary electronic equipment or devices (such as audio visual equipment, office-automation equipment, communications devices, electrical appliances and electronic toys).

Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), please be sure to consult with our sales representative in advance.

About Export Control Order in Japan

Products described herein are the objects of controlled goods in Annex 1 (Item 16) of Export Trade Control Order in Japan.

In case of export from Japan, please confirm if it applies to "objective" criteria or an "informed" (by MITI clause) on the basis of "catch all controls for Non-Proliferation of Weapons of Mass Destruction.