

Double-Edged Screw Extractors from Rennsteig



Product Specification

- for unscrewing damaged screws and bolts without damaging threads
- for both right and left handed threads
- non-slip and double-edged engagement with the screw being removed

The Double-Edged Screw Extractor represents a new generation of its kind used to remove damaged screws or bolts out of threads.

The Screw Extractors have four double-edged cutting edges. Only the two opposite edges engage with the screw to be removed.

This technology is perfect for use with both right and left handed threads.

Application

- mark the screw / bolt to be removed by using the centering point of the Screw Extractor
- open the screw / bolt by boring with an adequate drill
- drive the Screw Extractor into the bore hole until the cutting edges are in full contact with the object
- use a wrench to remove the object out of the thread hole by turning the screw extractor clockwise or counterclockwise
- after unscrewing, remove the damaged screw / bolt from the Screw Extractor

Centering point
for centering of bore

Cutting edges
for non-slip engagement

Hexagonal driving flat
for optimum torque



Rennsteig is a division of the KNIPEX Group that specializes in the manufacturing and development of high quality tools. For over 30 years, Rennsteig has been manufacturing products designed for maximum performance, ease of use and long life.



Double-Edged Screw Extractors from Rennsteig



Range of Delivery

The Double-Edged Screw Extractor is available in 7 different sizes!



Art.-No.	Size	sw mm	Drill Ø mm		Screw Sizes		sw Inch	Drill Ø Inch		Screw Sizes Inch		scales ounces	box icon
			min	max	min	max		min	max	min	max		
9R 471 001 3	1	6.3	3.2	4.8	M5	M6	1/4"	1/8"	3/16"	10"	1/4"	0.3	10
9R 471 002 3	2	10	4.8	7.1	M8	M10	3/8"	1/4"	9/32"	5/16"	3/8"	0.6	10
9R 471 003 3	3	13	6.4	9.5	M10	M12	1/2"	1/4"	3/8"	7/16"	1/2"	1.2	10
9R 471 004 3	4	16	8.7	12.7	M12	M16	5/8"	11/32"	1/2"	1/2"	9/16"	2.0	10
9R 471 005 3	5	19	11.1	15.9	M16	M20	3/6"	7/16"	5/8"	5/8"	3/4"	3.1	10
9R 471 006 3	6	22	14.3	19.1	M20	M24	7/8"	9/16"	3/4"	7/8"	1"	4.6	5
9R 471 007 3	7	26	19.1	23.8	-	M30	1"	3/4"	15/16"	1"	>1"	7.2	5

Packaging Options



Individual Item in
Transparent Plastic Case



Size 1-5 in Vinyl Pouch
Art.-No. 9R 471 900 3



Size 1-5 in Metal Case
Art.-No. 9R 471 900 3