



Product

The P-14 humidity sensor was specially developed to satisfy the wide range of applications in HVAC, tests and measurement, white goods and industrial field. By the consistent use of state-of-the-art production technologies and our extensive know-how in the field of high performance polymers, we have succeeded in producing a high quality sensor with an almost linear characteristic. The possibility of selecting the electrical connections provides users with ideal opportunities for implementing their own sensor design without limitation.



Advantages

- High humidity stability
- Low drift
- Condensation resistant – fast recovering time after dewing, and at high dew point temperatures as well
- High chemical resistance
- Wide temperature operating range
- Various wired solutions available

Technical Data

Wired



SMD



Humidity Operating Range:	0 ... 100% RH	0 ... 100% RH
Operating Temperature Range:	-50 ... +150 °C	-50 ... +150 °C
Capacitance (C_{30}) (at 23 °C and 30% RH):	150 pF ± 50 pF	180 pF ± 50 pF
Sensitivity (15 ... 90% RH):	0.25 pF / % RH (at $C_{30} = 150$ pF)	0.30 pF / % RH (at $C_{30} = 180$ pF)
Loss Factor (at 23 °C, at 10 kHz, at 90% RH):	< 0.01	< 0.01
Linearity Error (15 ... 90% RH at 23 °C, after one-point calibration):	< 1.5% RH	< 1.5% RH
Hysteresis: 1 h, 20% RH bei 23 °C → 1 h, 85% RH bei 70 °C → 1 h, 20% RH bei 23 °C	< 1.5% RH	< 1.5% RH
Response Time t_{63} (50% RH → 0% RH) at 23 °C:	< 5 s	< 5 s
Frequency Range:	1 ... 100 kHz (recommended 10 kHz)	1 ... 100 kHz (recommended 10 kHz)
Maximum Operating Voltage:	< 12 V _{pp} AC	< 12 V _{pp} AC
Signal Form:	alternating signal without DC bias	alternating signal without DC bias
Connectors:	Wires or customer specific	SMD




INNOVATIVE SENSOR TECHNOLOGY




Capacitive Humidity Sensor

Construction Sizes


Wired (in mm)



SMD (in mm)



Allowed Humidity-Temperature Range, operating conditions at atmospheric pressure (1 bar)



Sensor Characteristic

Capacitance [pF]

