
Item no.: 280-994
Product description: 4-conductor Ex e II through terminal block SUITABLE FOR EX
E APPLICATIONS



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	0.2 - 2.5 mm ²
Cross section [AWG]	24 - 12 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	550 V
Current intensity EN	20 A
Weight	9.156 g
Color	light gray
Wiring type	Front-entry
No. of connection Points	4
No. of potentials	1
Height	28 mm
Height	1.1 in
Width	5 mm
Width	0.197 in
Depth	75 mm
Depth	2.95 in
Strip length from	8 mm
Strip length to	9 mm

Strip length
Mounting

0.33 in
TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
280-994	ABS	05-HG476175/3-PDA	800	24	2,5
280-994	AEX	E185892	550	20	28-12
280-994	BV	07436/Co	800	24	2,5
280-994	CCA	NL5855	800	24	2,5
280-994	CSA	154112-1536071	600	15	28-12
280-994	DNV	E-10423	800	24	2,5
280-994	GL	17295-00HH	800	24	2,5
280-994	GOSENERGO-Ex	99.041	550	20	2,5
280-994	KEMA	2082859.07	800	24	2,5
280-994	LR	91/20112(E6)	800	24	2,5
280-994	PRS	TE/1718/880590/08	800	24	2,5
280-994	PTB	PTB99AteX3109U	550	20	2,5
280-994	RMR	11130002	800	24	2,5
280-994	RosTest	8189158	550	20	2,5
280-994	UR	E45172	600	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected