




**Compact Size  
Panel Mount Indicator, Non-Relampable  
LED Technology  
Mounting Hole, Ø 0.310"**



All dimensions are in inches



Minimum panel thickness: 0.030"

6" leads with 1/2" strip are standard  
Due to compact size, components (resistors, diodes)  
will be installed in the leads.

Storage temperature  $T_{STG}$  : -25°C - +80°C  
Ambient temperature  $T_A$  : -20°C - +60°C  
Voltage tolerance  $V_{OP}$  : ±10%

Part No.	Lens Color	Voltage (DC)	Current (mA)	Rated Life
<b>LED 6V Series</b>				
WL-2191SL1-6V	Red	5V-6V	20mA	100,000 Hrs
WL-2191SL5-6V	Green	5V-6V	20mA	100,000 Hrs
WL-2191SL6-6V	Blue	5V-6V	20mA	100,000 Hrs
WL-2191SL7-6V	Yellow	5V-6V	20mA	100,000 Hrs
<b>LED 12V Series</b>				
WL-2191SL1-12V	Red	12V-14V	20mA	100,000 Hrs
WL-2191SL5-12V	Green	12V-14V	20mA	100,000 Hrs
WL-2191SL6-12V	Blue	12V-14V	20mA	100,000 Hrs
WL-2191SL7-12V	Yellow	12V-14V	20mA	100,000 Hrs
<b>LED 24V Series</b>				
WL-2191SL1-24V	Red	24V-28V	20mA	100,000 Hrs
WL-2191SL5-24V	Green	24V-28V	20mA	100,000 Hrs
WL-2191SL6-24V	Blue	24V-28V	20mA	100,000 Hrs
WL-2191SL7-24V	Yellow	24V-28V	20mA	100,000 Hrs

Body Material: Nylon, white  
Lens Material: Polycarbonate  
Bezel Material: Chrome  
Wire Gauge: 18 AWG  
Wire Strip: 1/2"  
Anode(+): Red lead  
Notes: Tinnerman clips available separately.

Certifications: Most Wamco indicators carry Agency approvals. Please contact Wamco for the latest Agency information regarding the specific product series and voltage required.  
Options: Additional options and lens styles available. Please contact Wamco for more information.

<b>Drawn</b>	SC	04/04/12	<b>Compact Size Panel Mount Indicators LED</b>	<b>Datasheet:</b> WL-2191SLX-XXX Series	<b>Rev:</b> 1
<b>Checked</b>	EB	04/04/12			
<b>Approved</b>	EB	04/05/12			