


Item no.: 750-402
 Product description: 4-CHANNEL DIGITAL INPUT MODULE DC 24 V 3,0 ms
 POSITIVE SWITCHING 2- TO 3-CONDUCTOR-CONNECTION



Produkt kann von Bild abweichen / product may differ

Packing unit 1 piece

RoHS compliant

Product group	15 (I/O System)
No. of inputs	4
CURRENT CONSUMPTION (INTERNAL)	7.5 mA
Voltage via power jumper contacts (max)	DC 24 V (-25% / + 30%)
Signal voltage (0)	DC -3 V ... +5 V
Signal voltage (1)	DC 15 V ... 30 V
Input filter (ms)	3 ms
Current supply (typ)	4.5 mA
Isolation	500 V system / supply
Internal data width (Bit)	4 Bit
Operating temperature	0 °C ... + 55 °C
Storage temperature	-25 °C ... +85 °C
Relative air humidity	95 %
Vibration resistance	acc. IEC 60068-2-6
Shock resistance	acc. IEC 60068-2-27
Degree of protection	IP 20
EMC marine applications - noise proof	gem. Germanischer Lloyd (2003)
EMC marine applications - noise transmission	gem. Germanischer Lloyd (2003)
Conformity marking	CE

Approvals

Cross section [mm²]

Cross section [AWG]

ATEX

0.08 - 2.5 mm²

28 - 14 AWG



Connection method	CAGE CLAMP® CONNECTION
Weight	48.5 g
Color	light gray
Height	64 mm
Height	2.52 in
Width	12 mm
Width	0.472 in
Depth	100 mm
Depth	3.937 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
750-402	ABS	03-HG374860/3-PDA			
750-402	BSH	Bescheinigung Nr. 467			
750-402	DNV	A-12306			
750-402	GL	26 898 - 05 HH			
750-402	IECEX	IECEX PTB 07.0064X			
750-402	LR	02/20026 (E2)			
750-402	NK	TA06190M			
750-402	PRS	TE/1720/880590/08			
750-402	Rina	ELE153207CS001			
750-402	UL	E175199 Sec.1			
750-402	UL	E198726 Sec.1			
750-402	UL DEMKO A/S	08 ATEX 142851 X			

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected