STM32 32-bit ARM Cortex MCUs Releasing your creativity






STM32 platform

32-bit Flash microcontrollers powered by the ARM® Cortex[™]-M processor

The STM32 family of 32-bit Flash microcontrollers based on the ARM Cortex[™]-M processor is designed to offer new degrees of freedom to MCU users. By bringing a complete 32-bit product range that combines high-performance, real-time, low-power and low-voltage operation, while maintaining full integration and ease of development, the STM32 family helps you create new applications and design in the innovations you have long been dreaming about.

FIVE REASONS TO CHOSE THE STM32 PLATFORM

More than 350 compatible devices



STM32, A SOLID FOUNDATION FOR GROWTH

With the STM32, ST offers a comprehensive portfolio of advanced MCUs that we are committed to extending in capability, competitive pricing and features to cover the needs of developers.





ADDRESSING THE THREE DIMENSIONS OF MICROCONTROLLER CONTENT

With its broad range of products, the STM32 addresses the three dimensions of microcontrollers: performance, low power and cost sensitiveness.



High-performance MCUs with DSP and FPU

- STM32 F4 series based on Cortex-M4 with up to 168 MHz/210 DMIPS
- ART Accelerator[™] and 7-layer bus matrix
- Low dynamic consumption: 230 µA/MHz
- HS-USB, IEEE 1588 Ethernet, camera interface

Mixed-signal MCUs with DSP and FPU

- STM32 F3 series based on Cortex-M4 with up to 72 MHz/62 DMIPS (from Flash) or 94 DMIPS (from CCM-SRAM)
- Up to 48-Kbyte SRAM and CCM-SRAM
- Rich analog peripherals plus low-/mid-density memory: 7x comparators, 4x PGA, 4x 12-bit ADC (5 MSPS), 3x 16-bit $\Sigma\Delta$ ADC and 2x 3-phase MC timer (144 MHz)



High-performance MCUs

- STM32 F2 based on Cortex-M3 up to 120 MHz/150 DMIPS
- ART Accelerator[™] and 7-layer bus matrix
- Low dynamic consumption: 188 μA/MHz
- HS-USB, IEEE 1588 Ethernet, camera interface

Mainstream MCUs

- Based on Cortex-M3 running up to 72 MHz
- Large peripheral set: ADC and DAC, 12 bits, comm peripherals (USART, USB, SPI, I²C and more), multiple timers, maximum integration

Entry-level MCUs

- STM32 F0 based on Cortex-M0 up to 48 MHz/38 DMIPS
- ADC and DAC, 12 bits, comparator
- Communication peripherals (USART, SPI, I²C FM+ and HDMI CEC)
- 3-phase motor control

Ultra-low-power MCUs



- STM32 L1 ultra-low-power platform
- Low voltage down to 1.65 V
- 32 MHz processing performance
- Ultra-low static consumption
 - 0.45 µA Stop mode
 - 0.3 µA Standby mode

Wireless MCUs, IEEE 802.15.4



- STM32 W based on Cortex-M3 running up to 24 MHz
- 2.4 GHz IEEE 802.15.4 transceiver and lower MAC with excellent Wireless performance:
 - Rx sensibility up to -100 dBm
 - Output power configurable up to +8 dBm
- Low-power-mode consumption: 0.4 µA with RAM retention



STM32 PRODUCT LINES

ommon core peripherals	STM32 F4 series - High performance with DSP (STM32F405/415/407	7/417)
d architecture: Communication peripherals: USART, SPI, I ² C	168 MHz Cortex-M4 with DSP and FPUUp to 192-KbyteUp to 1-Mbyte Flash2x USB 2.0 0TG FS/HS3-phase MC timer2x CAN 	SDIO 2x I ² S audio Camera IF Ethernet IEEE 1588 Crypto/ hash processor and RNG
Multiple general-	STM32 F3 series - Mixed-signal with DSP (STM32F302/303/313/372	/373/383)
purpose timers Integrated reset and brown-out warning	72 MHzUp to 48-KbyteUp to 256-Kbyte2x USB 2.0 FS2x 3-phase MC timer (144 MHz)	Up to 7x S ADC 4x PGA STM32 F3
Multiple DMA	STM32 F2 series - High performance (STM32F205/215/207/217)	
2x watchdogs Real-time clock Integrated regulator PLL and clock circuit	120 MHzUp to Cortex-M3Up to 128-KbyteUp to 1-Mbyte2x USB 2.0 0TG Flash3-phase MC timer2x CAN 2.0B	SDIO 2x I ² S audio Camera IF Ethernet IEEE 1588 Crypto/ hash processor and RNG
External memory	STM32 F1 series - Mainstream - 5 product lines (STM32F100/101/10)2/103 and 105/107)
interface (FSMC)	Up to 72 MHz Cortex-M3 CPUUp to 96-Kbyte SRAMUp to 1-Mbyte FlashUSB 2.0 0TG FS3-phase MC timerUp to 2x CAN 2.0B	SDIO 2x I ² S audio Ethernet IEEE 1588
	STM32 F0 series – Entry level (STM32F050/051)	
Main oscillator and 32 kHz oscillator Low-speed and high-speed internal RC oscillators	48 MHz Up to Cortex-M0 8-Kbyte SRAM Up to CPU CPU CPU CPU CPU CPU CPU CPU CPU CPU	STM32 F0
	STM32 L1 series - Ultra-low-power (STM32L151/152/162)	
-40 to +85 °C and up to 105 °C operating temperature range	32 MHz Cortex-M3 CPUUp to 48-KbyteUp to 384-KbyteUSB FS deviceUp to 12-KbyteLCD 8x40 EEPROM	Comparator BOR AES MSI VScal 128-bit
Low voltage 2.0 to 3.6 V	STM32 W series - Wireless (STM32W108)	
or 1.65/1.7 to 3.6 V (depending on series) Temperature sensor	24 MHz Cortex-M3Up to 16-KbyteUp to 256-Kbyte2.4 GHz IEEELower MAC Digital basebandAES 128-bit	STM32 W


FS:	Full speed	MSI:	Multi-speed internal oscillator	VScal:	Voltage scaling
HS:	High speed	RNG:	Random number generator	FPU:	Floating point unit
MC:	Motor control	SDIO:	Secure digital input/output	DSC:	Digital signal controller

STM32, THE OPTIMAL PLATFORM CHOICE

The STM32 is the optimal choice to support many applications with the same platform.

All product lines in the seven series are pin-to-pin and software compatible, making it easy to upgrade to a higher or downgrade to a lower memory size. Numerous applications may be addressed using the sole STM32 platform.

STM32 PORTFOLIO



STM32 F4 SERIES BLOCK DIAGRAM

This block diagram shows all the available peripherals. For exact product content, refer to the device summary.

	ART Accelerator™	Up to 1-Mbyte Flash memory
System		Up to 192-Kbyte SRAM
Power supply 1.2 V regulator POR/PDR/PVD		FSMC/ SRAM/NOR/NAND/CF/ LCD parallel interface
Xtal oscillators 32 kHz + 4 to 26 MHz	ARM Cortex-M4 168 MHz	80-byte + 4-Kbyte backup SRAM
Internal RC oscillators 32 kHz + 16 MHz		512 OTP bytes
PLL		Connectivity
Clock control	Floating point unit (FPU)	Camera interface
RTC/AWU	Nested vector	3x SPI, 2x I ² C, 3x I ² C
SysTick timer	interrupt	Ethernet MAC 10/100
2x watchdogs (independent and window)	controller (NVIC)	with IEEE 1588
	MPU	2x CAN 2.0B
51/82/114/140 I/Os	JTAG/SW debug/ETM	1x USB 2.0 OTG FS/HS ¹
Cyclic redundancy check (CRC)		1x USB 2.0 OTG FS
	Multi-AHB bus matrix	SDIO
	16-channel DMA	6x USART LIN, smartcard, IrDA, modem control
Control 2x 16-bit motor control	Crypto/hash processor ²	
Synchronized AC timer 10x 16-bit timers 2x 32-bit timers	3DES, AES 256	Analog
	SHA-1, MD5, HMAC	2-channel 2x 12-bit DAC
		3x 12-bit ADC 24 channels/2.4 MSPS
	True random number generator (RNG)	Temperature sensor

APPLICATIONS

- Industrial
 - PLC
 - Inverters
 - Printers, scanners
 - Industrial networking
 - Solar inverters
- Building and security
 - Alarm systems
 - Access control
 - HVAC
 - Power meters
- Medical
 - Glucose meters
 - Portable medical care
 - VPAP, CPAP
- Patient monitoring
- Appliances
 - 3-phase motor drives
 - Application control
 - User interfaces
 - Induction cooking
- Consumer
 - Home audio
 - Gaming
- PC peripherals
- Digital cameras, GPS

1. HS requires an external PHY connected to the ULPI interface 2. Crypto/hash processor on STM32F417 and STM32F415

SUPERIOR AND INNOVATIVE PERIPHERALS


Peripherals	STM32 F4 series	STM32 F3 series	STM32 F2 series	STM32 F1 series	STM32 F0 series	STM32 L1 series	STM32 W series
The need for speed							
USB FS	12 Mbit/s	12 Mbit/s	12 Mbit/s	12 Mbit/s	Consumer electronics control for consumer devices	12 Mbit/s	-
USB HS	480 Mbit/s	-	480 Mbit/s	-	-	-	-
USART	Up to 10.5 Mbit/s	Up to 6 Mbit/s	Up to 7.5 Mbit/s	Up to 4.5 Mbit/s	Up to 6 Mbit/s	Up to 4 Mbit/s	Up to 1 Mbit
SPI	Up to 37.5 Mbit/s	Up to 18 Mbit/s	Up to 30 Mbit/s	Up to 18 Mbit/s	Up to 18 Mbit/s	Up to 16 Mbit/s	Up to 12 Mbit/s
l²C	400 kHz	1 MHz	400 kHz	400 kHz	1 MHz	400 kHz	400 kHz
GPI0	Up to 60 MHz	Up to 18 MHz	Up to 60 MHz	Up to 18 MHz	Up to 12 MHz	Up to 16 MHz	Up to 12 MHz
3-phase MC timer	168 MHz PWM timer clock input	144 MHz PWM timer clock input	120 MHz PWM timer clock input	72 MHz PWM timer clock input	48 MHz PWM timer clock input	-	-
SDI0	Up to 48 MHz	-	Up to 48 MHz	Up to 48 MHz	-	Up to 48 MHz	-
I²S	From 8 kHz to 96 kHz sampling frequencies	From 8 kHz to 96 kHz sampling frequencies	-				
Camera interface	Up to 54 Mbyte/s at 54 MHz	-	Up to 48 Mbyte/s at 48 MHz	-	-	-	-
Crypto/hash processor	AES-256 up to 149.33 Mbyte/s	-	AES-256 up to 106 Mbyte/s	-	-	AES-128 up to 2.4 Mbyte/s	AES-128 up to 2.4 Mbyte/s
FSMC	Up to 60 MHz	-	Up to 60 MHz	Up to 36 MHz	-	Up to 32 MHz	-

SUPERIOR AND INNOVATIVE PERIPHERALS (CONT'D)

Peripherals	STM32 F4 series	STM32 F3 series	STM32 F2 series	STM32 F1 series	STM32 F0 series	STM32 L1 series	STM32 W series
The need for analog							
ADC conversion time	0.41 μs (2.4 MSPS)	0.2 µs (5 MSPS), (50 kSPS)	0.5 µs (2 MSPS)	1 µs (1 MSPS)	1 µs (1 MSPS)	1 µs (1 MSPS)	5.3 µs (188 kSPS)
ADC accuracy	12-bit	12- or 16-bit	12-bit	12-bit	12-bit	12-bit	12-bit
DAC	2-channel, 12-bit	2- channel, 12-bit	2-channel, 12-bit	2-channel, 12-bit	1-channel, 12-bit	2-channel, 12-bit	-
			The need fo	r connectivity			
CAN	Up to 2 independent CAN	Up to 2 independent CAN	Up to 2 independent CAN	Up to 2 independent CAN	-	-	-
Ethernet	10/100 Mbit/s MAC with hardware IEEE 1588	-	10/100 Mbit/s MAC with hardware IEEE 1588	10/100 Mbit/s MAC with hardware IEEE 1588	-	-	-
USB OTG	Full speed and high speed host, device or OTG	-	Full speed and high speed host, device or OTG	Full speed and high speed host, device or OTG	-	-	-
CEC bus	-	Consumer electronics control for consumer devices	-	Consumer electronics control for consumer devices	Consumer electronics control for consumer devices	-	-
Flexible static memory	4 independent banks, 8/16-bit data bus, supports SRAM, PSRAM, NAND and NOR Flash, parallel graphic LCD	-	4 independent banks, 8/16-bit data bus, supports SRAM, PSRAM, NAND and NOR Flash, parallel graphic LCD	4 independent banks, 8/16-bit data bus, supports SRAM, PSRAM, NAND and NOR Flash, parallel graphic LCD	-	4 independent banks, 8/16-bit data bus, supports SRAM, PSRAM, NAND and NOR Flash, parallel graphic LCD	-
Camera interface	8- to 14-bit parallel	-	8- to 14-bit parallel	-	-	-	-
RF	-	-	-	-	-	-	2.4 GHz IEEE 802.15.4 transceiver and lower MAC

OUSTANDING PERFORMANCE: 210 DMIPS/501 COREMARK EXECUTING FROM FLASH AT 168 MHZ OPERATING FREQUENCY


ART Accelerator[™] performance result



OUTSTANDING LOW-POWER PERFORMANCE

STM32 F4 series power consumption






Note:

- Executing Coremark benchmark from Flash with peripherals disabled

STM32 L1 series power consumption

Typical current

(@ 25 °C)



Notes:

- POR/PDR on

- RAM content preserved

- BOR option at 2.4 µA

- Startup time from Stop 8 µs

- Run and Sleep consumption value are independent of VDD

Stop and standby values measured at $V_{DD} = 1.8 \text{ V}$

- Low-power Run and low-power Sleep are measured with Flash off

MOTOR CONTROL

The STM32 is perfectly suited to 3-phase brushless single or dual motor control:

- Advanced PWM timer, fast ADC, high-performance core
- Class B compliancy with the EN/IEC 60335-1 norm
- Single or dual motor control



The STM32's motor control ecosystem brings:

- Free 3-phase motor control software development kit (firmware and graphical customization tool) supporting AC induction motors (sensored) and PMSM motors (sensorless, Hall sensor or encoder) for vector control (field oriented control)
- Full developer vector drive PMSM motor control kits (hardware and firmware) based on the STM32F103 (order code: STM3210B-MCKIT) or STM32F100 (order code: STM32100B-MCKIT)
- Digital PFC and dual FOC drive demo, free RTOS example
- STM Studio tool to monitor data in the user code when the motor control algorithm is running



Development tools

ST's STM32 family of 32-bit ARM Cortex[™]-M-core-based microcontrollers are supported by a complete range of low-cost and high-end, evaluation software, debugging and programming tools. This complete line includes third-party solutions that come complete with C/C++ compiler, integrated development environment and in-circuit debugger/programmer featuring a JTAG /SWD application interface. Developers can also explore and start applications easily with any of a range of affordable, easy-to-use starter kits.

The superb combination of a state-of-the-art and efficient library of software drivers and extensive support for all major tool providers offers a fast route to best fit and an optimized development process.

START TODAY WITH STM32-DISCOVERY KITS

Discovery kits are the cheapest and quickest way to discover the STM32 family. These quick-start evaluation boards embed an ST-LINK or ST-LINK/V2 debug probe and are supported by IDE from Atollic, Keil, IAR and TASKING.

STM32 F3 series (order code: STM32F3DISCOVERY)

The STM32F3-Discovery is the perfect kit to discover not only the richness of the STM32 F3 series, but also ST's MEMS gyroscope and e-compass.

STM32 F4 series (order code: STM32F4DISCOVERY)

To discover the STM32 F4 series, the STM32F4-Discovery highlights the performances of the F4 series with audio (input, output) and USB Host capabilities.

STM32 F1 series (order code: STM32VLDISCOVERY)

Based on the STM32 F1 series Value line, the STM32 Value line Discovery kit will satisfy hobbyists, first-time developers and students.

STM32 F0 series (order code: STM32F0DISCOVERY)

Discover the STM32 F0 series based on the Cortex-M0 core. A prototyping board is included for easy connection of additional components and modules.

STM32 L1 series (order code: STM32L-DISCOVERY)

Based on the STM32 L1 series, the STM32L-Discovery kit includes a 6-digit LCD display, a touch-sensing slider, 2 LEDs, a user button and current measurement.

STM32 EVOPRIMER

Play, explore and develop applications on the EvoPrimer with Raisonance toolset, free demos and an online community at www.stm32circle.com to stimulate creative designs. Order codes: STM3240GPRIMER (STM32 F4 series) STM3210CPRIMER (STM32 F1 series Connectivity line) STM3210GPRIMER (STM32 F1 series Performance line)

STM32L15PRIMER (STM32 L1 series)



STM32F3DISCOVERY





STM32F4DISCOVERY

STM32F0DISCOVERY





STM32VLDISCOVERY

STM32L-DISCOVERY



STM32-COMSTICK

Evaluate STM32 networking features of the STM32 Connectivity line with STM32-ComStick (order code: STM32-COMSTICK). This kit includes an integrated debugging/programming capability via USB and unlimited Hitex HiTOP5 and TASKING VX C compilers.

STM32W RF CONTROL KIT

Low-cost RF control kit: The STM32W RF Control Kit is a low-cost and quick way to get started using STM32W-based point-to-point wireless control applications. Order code: STM32WC-RFCKIT

STARTER KITS FOR STM32

Part number	Featured product	Description			
STM3210B-SK/HIT	STM32F103RBT6	Hitex kit with unlimited HiTOP5, TASKING VX compilers, STM32-PerformanceStick with integrated debugging/programming			
STM3210E-SK/HIT	STM32F103VET6	via USB, extension I/O board with peripheral evaluation features, DashBoard GUI			
STM3210C-SK/IAR	STM32F107VCT6				
STM3210E-SK/IAR	STM32F103ZET6				
STM32L152-SK/IAR	STM32L152VBT6	IAR Embedded Workbench for ARM (for up to 32 Kbytes of code), IAR C/C++ compiler, J-Link (USB/JTAG), evaluation board			
STM3220G-SK/IAR	STM32F207ZGT6	TAN ETIDEQUED WORKDETCH TOF ANIM (TOF UP to 52 KUYLES OF COUP), TAN C/C++ COMPILER, J-LITIK (USB/JTAD), EVALUATION DUALU			
STM320518-SK/IAR	STM32F051R8T6				
STM3240G-SK/IAR	STM32F407ZGT6				
STM3210C-SK/KEIL	STM32F107VCT6				
STM3210E-SK/KEIL	STM32F103ZET6	Keil Deelkiew MDK with wite at fear we to 20 Khutee of code). ADM C/C compiler UI INK (UCD/ ITAC), evoluati			
STM3220G-SK/KEI	STM32F207IGH6	Keil RealView MDK with µVision4 (for up to 32 Kbytes of code), ARM C/C++ compiler, ULINK (USB/JTAG), evaluation board			
STM3240G-SK/KEI	STM32F407IGH6				
STM3210B-SK/RAIS	STM32F103VBT6	Raisonance REva kit with RIDE (debug up to 32 Kbytes of code), GNU C/C++ compiler, modular evaluation hardware with			
STM3210C-SK/RAIS	STM32F107VCT6	integrated RLink (USB/JTAG)			
STM3210B-MCKIT	STM32F103VBT6	ST motor control starter kit with complete sensor and sensorless libraries, evaluation hardware platform for vector drive of			
STM32100B-MCKIT	STM32F100VBT6B	3-phase brushless magnet synchronous motors, plus Segger J-LINK for host PC interface			

EVALUATION BOARDS FOR STM32

Evaluation boards from ST implement the complete range of device peripherals for STM32 devices.

Part number	Featured product	
STM3240G-EVAL	STM32F407IGH6	
STM32303C-EVAL*	STM32F303VCT6	
STM32373C-EVAL	STM32F373VCT6	
STM3220G-EVAL	STM32F207IGH6	
STM3210C-EVAL	STM32F107VCT6	
STM3210E-EVAL	STM32F103ZGT6	
STM32100B-EVAL	STM32F100VBT6B	STM320518-EVAL
STM32100E-EVAL	STM32F100ZET6B	STIVISZUSTO-EVAL
STM320518-EVAL	STM32F051R8T6	
STM32L152-EVAL	STM32L152VBT6	
STM32L152D-EVAL	STM32L152ZDT6	Note: * Available in Q4/2012





M320518-EVAL



STM3240G-EVAL



STM32L152D-EVAL



STM32F373C-EVAL

STM32W EVALUATION KIT

Complete kit to evaluate the capabilities of the STM32W in different configurations: remote control (ZigBee RF4CE stack) and point-to-point network (simplified MAC library).

Main kit order code:

- STM32W108C-SK (256-Kbyte Flash device) Extension kit order code:
- STM32W108C-KEXT













STM32 SOFTWARE DEVELOPMENT TOOLS

Third-party solutions come complete with IDE, C/C++ compiler and JTAG debug probes. Development and debug of STM32 applications is made even easier with MicroXplorer, a free graphical tool to configure ST's MCUs, and STM-STUDIO, a free tool to monitor and visualize variables at runtime.

Java for STM32

Start developing applications for the STM32 in Java. Benefit from Java and the highlyoptimized STM32 Java virtual machine to increase software engineering productivity. Ideal for feature-rich applications with humanmachine interfaces and Internet protocol connectivity. ST order code:

STM3220G-JAVA (STM32 F2 series)

Microsoft .NET Micro Framework for STM32

After the NETMF for STM32 F1, the Mountaineer Group

(http://www.mountaineer.org/) has ported NETMF to the STM32 F2 and STM32 F4. This port presents drivers for the on-chip peripherals: GPIOs, analog inputs and outputs, I²C, SPI, UARTs, USB, internal Flash, power management, timers, and more. It is already available at the Codeplex site



(http://netmf.codeplex.com/) and will be integrated into Microsoft's Porting Kit (just like the F1 Edition) for the next version of NETMF 4.3. ST order codes: STM3240G-ETH/NMF (STM32 F4 series) and STM3240G-USB/NMF (STM32 F4 series).

STM32 software solutions

From the hardware abstraction layer, through middleware and up to the application field, the STM32 software ecosystem is extensive, providing a consistent set of solutions, coming from more than 20 partners, based on open-source, or even built in-house. All STM32 peripherals are functionally covered, including peripheral library, DSP library, crypto library, file systems, USB, Ethernet, Bluetooth, Wi-Fi, display, industrial, audio, motor control, and medical applications.

Contact your local ST sales and marketing office for more information on the solutions described in this document.

Hardware abstraction layer

STM32 standard peripheral library: Complete set of device drivers for all the standard device peripherals, with many examples.

CMSIS DSP library: Standardized interface, with more than 50 math operations (FIR, FFT, matrix, and more) accelerated with DSP instructions.

STM32 crypto library: Software implementation of cryptographic algorithms, optimized for STM32.

STM32 self-test routines Class B norm certification: Complete software for EN/IEC 60335-1 Class B norm.

Middleware

STM32 USB libraries: Complete firmware packages for USB, slave and host, with many covered classes.

STM32 TCP/IP stacks: Several stacks are available, such as LwIP or NicheLite. Partners offer more extensive protocol support, or other communication means such as Wi-Fi.

STM32 graphical library: Basic blocks to build a graphical interface (including combo boxes, textboxes, slide bars). Comes with a PC wizard to build your screens.

STM32 Bluetooth stack: iAnywhere full Bluetooth stack with many different profiles. With our partner Alpwise.

STM32 industrial protocols: Full range of supported industrial protocols: Profinet, EtherCAT, Modbus, DeviceNet, CANopen, and more, via our partner network.

Application fields

STM32 audio solutions: Full range of audio software bricks, optimized for STM32: MP3 codec, MP3 decoder, WMA decoder, Speex speech codec, ADPCM compression, audio algorithms such as loudness control, channel mixer, 5-band equalizer, iPod/iPhone/ iPad interface through iAP (iPod Application Protocol) interface, USB synchronization methods for streaming, and more. Contact your sales office for information on availability for specific STM32 part numbers.

STM32 motor control software: Complete 3-phase motor-control software development kit (firmware and graphical customization tool) supporting single or dual PMSM motors in sensored and sensorless mode and AC induction motors in sensored mode, plus a patented single-shunt algorithm. This SDK is included in the STM32 motor control kits.

STM32 Continua certified solution: Software bricks to build up your Continua medical solution. Provided bricks are USB PHDC class (personal health device class), base framework protocol, glucose agent and thermometer agent. Further agents can be implemented on demand.



© STMicroelectronics - September 2012 - Printed in United Kingdom - All rights reserved The STMicroelectronics corporate logo is a registered trademark of the STMicroelectronics group of companies All other names are the property of their respective owners

