

## STRIPPING TOOLS

No.	Length mm	Length inches	Working range / Finish	Weight
-----	--------------	------------------	------------------------	--------

### Stripping and crimping tool

for easy stripping, crimping and cutting only with one tool, the special scanning system adjusts automatically to the wire diameter

5-532	160	6 1/4"	easy stripping from 0.5 to 6.0 mm <sup>2</sup> stripping length 5 mm crimping ranges for terminals: 0.5 to 2.5 and 4.0 to 6.0 mm <sup>2</sup> cutting capacity of the side cutters max. 6.0 mm <sup>2</sup> , solid conductors max. 4.0 mm <sup>2</sup>	115 g
-------	-----	--------	--	-------



### Coax cable stripper

for two-or-three-level stripping of all common coaxial cables (e.g. antenna- and transmission cables) and flexible cables

5-535	110	4 3/8"	coax cable from 4.8 to 7.5 mm outside-Ø for flexible cable 3 x 0.75 mm <sup>2</sup> , 10 mm <sup>2</sup> and 16 mm <sup>2</sup>	30 g
-------	-----	--------	--	------



### Round cable stripper

with ergonomical handles

5-536	125	5"	round and continental type cable from 8 to 13 mm Ø e.g. NYM 3 x 1.5 mm <sup>2</sup> up to 5 x 2.5 mm <sup>2</sup>	45 g
-------	-----	----	--	------



### Swivel-blade cable strippers

for accurate, fast and safe stripping of all common round cables of 4 - 28 mm Ø, cutting depth and adjustment via adjusting screw at end of handle, moving inner blade automatically adjusts itself from circular to longitudinal cuts

5-503	130	5 1/8"	without blade: 8 - 28 mm Ø	70 g
5-504	130	5 1/8"	without blade: 4 - 16 mm Ø	70 g
5-505	170	6 3/4"	hook blade: 4 - 28 mm Ø	80 g
5-506	180	7"	straight blade: 4 - 28 mm Ø	80 g



### Automatic wire stripper Super

fully insulated automatic wire stripper for all common stranded and solid conductors of 0.2 - 6.0 mm<sup>2</sup>, adjustable length stop of 5 - 12 mm, removable if required

5-531	200	8"	built-in side cutters for max. 2 mm Ø	105 g
15-531 VDE	200	8"	fibreglass re-enforced polyamide, fully insulated, approved for works on "hot" lines up to 1000 Volt	105 g