

Port Saver


Male-Female, HD, 15way



Specifications:

Voltage rating	: 300V AG(rms)
Current rating	: 5A continuous
Dielectric strength	: 1,000V AG
Minimum contact resistance	: 10mΩ
Minimum Insulation resistance	: 5,000MΩ
Durability	: 30 cycles for gol flash 150 cycles for 15μ" cold plated
Corrosion resistance	: Meet M-STD-202F method 101 conition bsalt water Spray or gold plated over 15μ"
Mating force insertion force	: OZ-16 OZ Average 150 gram Minimum extraction force: 1kg

Mini GC FD13M-F



Dimensions : Millimetres

Part Number Table

Description	Part Number
Port Saver, M-F, HD15way	AD-666

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.