


# Multicore Cables

## Sub Miniature - Screened



### Features:

- These standard, sub-miniature cables are manufactured to Ministry of Defence, Defence standard 61-12 Part 4 (for sub-miniature sizes)
- The cores have tinned conductors of high conductivity annealed copper insulated with PVC compound to BS6746 type 2. The screen is of braid construction conductivity tinned annealed copper wire. The fill factor of density of braid as defined in Def 61-12 parts 4 is not less than 0.7 for C type
- These multicore flexible cables are designed for high density wiring between components and within instruments and electronic equipment. They are extensively used in aircraft, avionic control systems, computers, data processors, process control systems, military vehicles and ancillary military equipment. Because of the mechanical design of these cables they should not be used for direct connection of equipment to mains power supplies.

### Technical Specifications:

Voltage rating	: 250 V (rms)
Maximum current per core	: 0.25 A
Conductor area	: 0.055 mm <sup>2</sup> per core
Maximum operating temperature	: 70°C
Sheath colour	: Grey
Nominal insulation radial thickness on core	: 0.2 mm
Nominal core resistance	: 348 Ω / Km, 20°C

### Specification Table


Number of Cores	Nominal Diameter		Length (m)	Type	Part Number
	Minimum	Maximum			
4	2.9	3.4	100	7-1-4C	860173 100M
15	5	5.4	25	7-1-15C	860183 25M
			100		860183 100M
25	6	6.6	25	7-1-25C	860128 25M

Dimensions : Millimetres (Unless Specified)

# Multicore Cables

## Sub Miniature - Screened

### Part Number Explanation:



**Nominal Diameter of Each Wire**

: 1 = 0.1 mm

**Number of Cores**

: 4, 15 and 25

**Type of Construction**

: C = Tinned Conductors Insulated with PVC to BS6746 Type 2, collectively screened braid construction using tinned, annealed copper wire. Fill factor of density of braid not to be less than 0.7 overall sheathed with PVC to BS6746 type 6.

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.