


BG1A Universal High Power IGBT Module Gate Driver Board

BG1A-F kit contents: M57160AL gate driver and VLA106-15242 DC/DC converter. BG1A-KA kit contents: VLA504 gate driver and VLA106-15242 DC/DC converter.

*The VLA504 replaces the older M57962L gate driver and the VLA106-15242 replaces the M57145L-01 DC/DC converter.





Description

BG1A is a fully isolated gate drive circuit board designed for use with high current single IGBT modules. When the board is populated, a VLA504 hybrid gate driver supplies the gate drive with complementary emitter follower power booster to provide efficient switching of modules rated up to 1200A. The hybrid gate drivers also provide protection against unexpected short circuit conditions. Isolated control power for the driver is supplied by an onboard VLA106-15242 regulated DC/DC converter. The fault feedback signal is also optically isolated. See application note "Hybrid Circuits Simplify IGBT Module Gate

Drive" at www.pwrx.com.

Features

- 20A Peak Output Current
- 2500VRMS Isolation
- Direct Mounting to IGBT
- +15V to –8.5V Output Voltage Swing
- Wide Input Voltage Range +12V to +18V


Applications Designed for use with the following Powerex Single IGBT Modules

- CM600HU-12H/F
- CM400/600HU-24H/F
- CM800/1000HA-24H
- CM800/1000HA-28H
- CM1200HA-24J

Rapid Design - Component List

Designation	Description	Value	Example Type
C1,C2	Power supply decoupling	150µF	Panasonic FC
	capacitors. Low impedance	35V	EEUFC1V151
	long life type.		
C3,C4	Low ESR polyester film or	1μF	Panasonic
	ceramic decoupling capacitors	50V	ECQV1H105J L
C5	DC to DC converter input	150µF	Panasonic FC
	decoupling capacitor. Low	35V	EEUFC1V151
	impedance long life type	0 to 000 - F	D-t- DDE
C6	Optional - For adjustment of short circuit protection trip time.	0 to 200pF 50V	muRata RPE Series
R1	Current limit for fault opto	4.7K .25W	Series
R2	Pull up for fault output	4.7K .25W	
RG	Series gate resistor - See	0.5Ω to	
RG	Powerex IGBT application	330	
	notes	0.5 to 2W	
D1, D2	Collector voltage detection	1A, 1000V	Motorola
· ·	diodes. Vrrm greater than	t _{rr} <100ns	MUR1100E
	IGBT Vces rating.		
DZ1, DZ2	Gate protection zeners	17V, 0.5W	1N5247
DZ3	Detect pin protection zener	30V, 0.5W	1N5256
Q1	NPN Booster transistor	15A, 80V	ONSemi
		ļ	D44VH10
Q2	PNP Booster transistor	15A, 80V	Motorola
- D.		ļ	D45VH10
OP1	Opto for fault signal isolation		NEC PS2501
CN1	MTA100 6 position right angle		AMP
CN2	header with locking ramp	<u> </u>	640457-6
	5/16" Ring Lug on 3.5" wire		AMP 34151
J1	Insert when using M57160AL with F-Series IGBT modules		
	and omit D1, D2, DZ1-DZ3		
	and onlin D1, D2, D21-D23		

Schematic Diagram



Typical Interface Circuit

