

Ceramic Disc Capacitor




Features:

- Capacitance has non linear temperature coefficient
- Large capacitance in small size
- Wide range of general purpose applications

Specifications:

Capacitance Range	: 100pF to 47000pF
Capacitance Tolerance	: $\pm 10\%$, +80% to -20%
Operating Temperature Range	: -25°C to 85°C (Y5P), 10°C to 85°C (Z5V)
Rated Working Voltage	: 50V
Dissipation Factor (tan θ) : Y5P	: $\tan \theta \leq 2.5\%$
Z5V	: $\tan \theta \leq 5\%$
Insulation Resistance (IR) at 25°C	: 10,000M Ω Min. or 200M Ω / μ F, whichever is smaller
Dielectric Strength	: 2.5 times the rated WVDC
Testing Parameters	: 1kHz $\pm 20\%$, 1.0 $\pm 0.2V_{RMS}$.



C:50V = 1.5

Dimensions : Millimetres

Capacitance Chart:

Temperature Characteristics	Part Diameter	Rated Voltage (V)	Capacitance		Maximum Dimension		
			Range (pF)	Tolerance	D	T	F
MCB (Y5P) +10%	5	U (50)	1,200 to 2,200	K	5.5	3.5	5
	6		2,700 to 3,300		6.5		
	7		3,900 to 4,700		7.5		
	8		5,600 to 6,800		8.5		
MCF (Z5V) +22% to -82%	5		1,000 to 5,600	Z	5.5		


Dimensions : Millimetres



Ceramic Disc Capacitor



Part Number Explanation:



Temperature Characteristics Code:

	MCB (Y5P)	MCF(Z5V)
T.C.(PPM/°C) or Capacitance Change (%)	+10%	+22% to -82%

Rated Voltage:

	U
Voltage	50V

Part Diameter:

Code	Diameter (mm)
5	5
6	6
7	7
8	8

Capacitance Code:

Code	Capacitance (pF)
101	100
221	220
331	330
471	470
102	1,000
222	2,200
332	3,300
472	4,700

Ceramic Disc Capacitor



Tolerance Code:

Code	Tolerance
K	±10%
Z	+80 to -20%

Lead Configuration Code - Bulk and Taping Package:

Bulk Lead Code	Taping Lead Code	Configuration and Dimension			
		Kinked/Straight	Lead Space (F)	Min. Lead Length (L)	Remarks
5	-	Straight	2.5	25	-
6	G or L	Straight	5.0	25	G = Ammo, L = Reel

Dimensions : Millimetres

Part Number Table:

Description	Part Number
Capacitor, 100pF 50V	MCBU5101K5
Capacitor, 220pF 50V	MCBU5221K5
Capacitor, 330pF 50V	MCBU5331K5
Capacitor, 470pF 50V	MCBU5471K5
Capacitor, 1nF 50V	MCBU5102K5
Capacitor, 2.2nF 50V	MCBU6222K6
Capacitor, 3.3nF 50V	MCBU7332K6
Capacitor, 4.7nF 50V	MCBU8472K6
Capacitor, 1nF 50V	MCFU5102Z5
Capacitor, 2.2nF 50V	MCFU5222Z5
Capacitor, 4.7nF 50V	MCFU5472Z5

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.