

Terminal Block

4Way, 15A




Specifications:

Current Rating	: 15A (300V AC)
Minimum Withstanding Insulation Voltage	: 2,000V AC
Insulation Resistance	: > 2,000MW (500V DC)
Operating Temperature	: -40°C to +105°C
Wire Range	: 14AWG to 22AWG
Screw Torque	: 12lb-inch
Connector Mounting	: Panel
Pitch Spacing	: 9.5mm
No. of Contacts	: 4
Contact Material	: Brass
Contact Plating	: Tin
Terminal Type	: Screw
Wire Area Size Max	: 2mm

Terminal Block

4Way, 15A



Dimensions

L	S
39.2	28.5

Dimensions : Millimetres

Number	Description	Material	Plating/Finish	Colour
1	Insulating Body	Polyamide 66	-	Black
2	Terminal	Brass	Tin Plated	-
3	Screw	Steel	Ni Plated	

Part Number Table

Description	Part Number
Terminal Block - 4 Way 15A	T44-BB11-04

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.