

Wheel Pneumatic



Features:

- Rib tyre pattern wheel roller bearing bore
- Pneumatic tyre on a black polypropylene centre
- Roller bearing bore
- Standard duty loads
- Zinc plated pressed steel castor housing
- Manual handling applications
- Suitable for all surfaces such as grass and earth
- Suitable for damp environments even when medium-harsh chemicals may be present
- Not recommended for use with organic solvents, chlorinated substances, hydrocarbons and mineral oils
- Temperature -20°C to +60°C

Specifications:

Wheel Dia	: 260mm
Carrying Capacity	: 200kg
Wheel Type	: Pneumatic
Hub Dia	: 25mm
Wheel Hub Width	: 74mm
Tread / Wheel Width	: 85mm

Part Number Table

Description	Part Number
Wheel, Pneumatic, 260mm	82 4602

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. DURATOOL is the registered trademark of the Group. © Premier Farnell plc 2012.

