


# Vertical Header 2 Way







## Specifications:

Connector Type	: Wire to Board
Contact Termination	: Crimp
Gender	: Header
No. of Contacts	: 2
No. of Rows	: 1
Pitch Spacing	: 1.25mm
Contact Resistance	: 20mΩ
Current Rating	: 1A
Insulation Resistance	: 100MΩ
Operating Temperature	: -40°C to +85°C
Voltage Rating	: 125V AC
Withstand Voltage	: 250V AC / Minute

## Material and Finish:

Insulator	: Nylon 6T
Contact Material	: Phosphor Bronze
Finish	: Tin Plated



P.C.B Layout

A	B
1.25	4.25

Dimensions : Millimetres

Dimensions : Millimetres

## Part Number Table

Description	Part Number
Header, Vertical, 2Way	1251SM-02

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.