

Cable Ties Polyamide 6.6 standard T18R



T-Series, Article number: 111-01910

Available in a wide range of materials, these cable ties all feature internal serrations allowing for a positive hold onto cable, hose and pipe bundles. The design of the head guarantees a high tensile strength whilst allowing a very low insertion force, this, combined with the bent tail design of many of the ties, ensures a simple and quick installation. Whilst easily installed by hand, manual and pneumatic (for high volume applications) tensioning tools are available to ensure a consistent and safe installation.

These cable ties are used for routing, bundling and securing of cables, pipes and hoses.



Catalogue page (Date of issue: April 2011)



All catalogue pages



Print

Base Data

Application Method	Quick, simple fixing by hand or with HellermannTyton tensioning tools
Application Tool	MK20, MK3PNSP2, MK7P, MK7, MK3SP
Colour	Black (BK)
Fixation Method (FF)	None
Identification Plate Position	none
Product Family	T-Series
Product Group	Cable Ties Polyamide 6.6 standard
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Type	T18R.NB3P
Variant	Inside Serrated

Product Dimensions

Bundle \varnothing max.	22.0 mm
Bundle \varnothing max. (imperial)	0.86 "
Bundle \varnothing min.	1.5 mm
Bundle \varnothing min. (imperial)	0.06 "
Length (L)	100 mm
Length (L) (imperial)	4 "
Min. Tensile Strength (lbs)	18 lbs
Min. Tensile Strength (N)	80 N
Thickness (T)	1 mm
Width (W)	2.5 mm
Width (W) (imperial)	0.1 "

Logistic and Packaging

Carton Quantity	32000 pcs.
EAN code	4031026104218
Pack Cont.	100
Quantity of Europallet	576000 pcs.
Quantity per	pc

Weight (Kg) 0.28 kg

Material and Specifications

Flammability	UL94 V2
Material	PA66
Material	PA66 T18R
Operating Temperature	-40 °C to +85 °C, intermittent +105 °C (for 500 h)
Specification	UL ZODZ2.E85319, DIN 30015954

© HellermannTyton 2013