

Product data sheet

Characteristics

LC1D50AD7

contactor TeSys LC1-D - 3 poles - AC-3 440V
50 A - coil 42 V AC

Main

Range of product	TeSys D
Product or component type	Contactor
Device short name	LC1D
Contactor application	Motor control Resistive load
Utilisation category	AC-1 AC-2 AC-3 AC-4
Control circuit type	AC
Coil type	Standard
Poles description	3P
Pole contact composition	3 NO
Control circuit voltage	42 V AC 50/60 Hz

Complementary

Coil technology	Without built-in bidirectional peak limiting diode suppressor
Protective cover	With
[Ie] rated operational current	50 A ≤ 60 °C AC AC-3 power circuit 80 A ≤ 60 °C AC AC-1 power circuit
Motor power kW	15 kW 220...240 V AC 50/60 Hz 22 kW 380...400 V AC 50/60 Hz 25 kW 415 V AC 50/60 Hz 30 kW 440 V AC 50/60 Hz 30 kW 500 V AC 50/60 Hz 33 kW 660...690 V AC 50/60 Hz
Motor power hp	3 hp 115 V 1P AC 60 Hz UL 3 hp 115 V 1P AC 60 Hz CSA 15 hp 230/240 V 3P AC 60 Hz CSA 15 hp 230/240 V 3P AC 60 Hz UL 15 hp 200/208 V 3P AC 60 Hz CSA 15 hp 200/208 V 3P AC 60 Hz UL 40 hp 575/600 V 3P AC 60 Hz CSA 40 hp 575/600 V 3P AC 60 Hz UL 40 hp 460/480 V 3P AC 60 Hz CSA 40 hp 460/480 V 3P AC 60 Hz UL 7,5 hp 230/240 V 1P AC 60 Hz UL 7,5 hp 230/240 V 1P AC 60 Hz CSA
Auxiliary contacts type	Mechanically linked IEC 60947-5-1 1 NO + 1 NC Mirror contact IEC 60947-4-1 1 NC
Auxiliary contact composition	1 NO + 1 NC
Control circuit voltage limits	0.3...0.6 Uc 60 °C drop-out 50/60 Hz 0.8...1.1 Uc 60 °C operational 50 Hz 0.85...1.1 Uc 60 °C operational 60 Hz
[Ui] rated insulation voltage	600 V UL power circuit 600 V CSA power circuit 600 V UL control circuit 600 V CSA control circuit 690 V IEC 60947-1 power circuit 690 V IEC 60947-1 control circuit
[Uimp] rated impulse withstand voltage	6 kV IEC 60947
Oversvoltage category	III
Mounting support	Plate Rail
Flame retardance	V1 UL 94

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Connections - terminals	EverLink BTR screw connectors power circuit 2 1...25 mm ² flexible without EverLink BTR screw connectors power circuit 2 1...25 mm ² flexible with EverLink BTR screw connectors power circuit 2 1...25 mm ² solid without EverLink BTR screw connectors power circuit 1 1...35 mm ² solid without EverLink BTR screw connectors power circuit 1 1...35 mm ² flexible with EverLink BTR screw connectors power circuit 1 1...35 mm ² flexible without Screw clamp terminal control circuit 1 1...4 mm ² flexible without Screw clamp terminal control circuit 2 1...4 mm ² flexible without Screw clamp terminal control circuit 1 1...4 mm ² flexible with Screw clamp terminal control circuit 2 1...2,5 mm ² flexible with Screw clamp terminal control circuit 1 1...4 mm ² solid without Screw clamp terminal control circuit 2 1...4 mm ² solid without
Tightening torque	5 N.m power circuit EverLink BTR screw connectors 1...25 mm ² hexagonal 4 mm 8 N.m power circuit EverLink BTR screw connectors 35 mm ² hexagonal 4 mm 1,7 N.m control circuit screw clamp terminal flat Ø 6 mm 1,7 N.m control circuit screw clamp terminal Philips No 2 2 mm
[Ue] rated operational voltage	<= 690 V AC 25...400 Hz power circuit
[Ith] conventional free air thermal current	10 A ≤ 60 °C control circuit 80 A ≤ 60 °C power circuit
Irms rated making capacity	140 A AC control circuit IEC 60947-5-1 900 A 440 V power circuit IEC 60947
Rated breaking capacity	900 A 440 V power circuit IEC 60947
Associated fuse rating	10 A gG control circuit IEC 60947-5-1 100 A gG <= 690 V type 1 power circuit 100 A gG <= 690 V type 2 power circuit
Average impedance	1,5 mOhm 50 Hz 80 A power circuit
Power dissipation per pole	3,7 W AC-3 9,6 W AC-1
Inrush power in VA	140 VA 20 °C 0,75 60 Hz 160 VA 20 °C 0,75 50 Hz
Hold-in power consumption in VA	13 VA 20 °C 0,3 60 Hz 15 VA 20 °C 0,3 50 Hz
Operating time	4...19 ms opening 12...26 ms closing
Safety reliability level	B10d 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical durability	6000000 cycles
Operating rate	3600 cyc/h ≤ 60 °C
Minimum switching current	5 mA control circuit
Minimum switching voltage	17 V control circuit
Non-overlap time	1,5 ms on de-energisation between NC and NO contacts 1,5 ms on energisation between NC and NO contacts
Insulation resistance	> 10 MΩ control circuit
Height	122 mm
Width	55 mm
Depth	120 mm
Product weight	1,4 kg

Environment

Standards	CSA C22-2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508
Product certifications	BV CCC CSA DNV (Det Norske Veritas) GL GOST LROS (pending) RINA UL
IP degree of protection	IP2x VDE 0106 IP2x IEC 60529
Protective treatment	TH IEC 60068 3
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-60...80 °C
Permissible ambient air temperature around the device	-40...70 °C at Uc
Operating altitude	3000 m without
Fire resistance	850 °C IEC 60695-2-1
Shock resistance	10 gn contactor opened 15 gn contactor closed
Vibration resistance	2 gn contactor opened 5...300 Hz 4 gn contactor closed 5...300 Hz
Heat dissipation	4...5 W 50/60 Hz control circuit
RoHS EUR conformity date	0001
RoHS EUR status	Compliant