

U.I. Lapp GmbH	PRODUCT INFORMATION	
	SKINTOP® STR	12.09.2012

High oil-resistance for maximum reliability
 Permanent vibration protection
 Optimum strain relief
 Wide, variable clamping ranges
 Various accessories (e.g. multiple sealing inserts)



Application range

With reducing seal insert, to seal cables with smaller outer diameters.

Design

PG connection thread

Approvals (Norm references)

UL File Nr. E79903

Note

Refer to SKINTOP® PG accessories for suitable accessories
 Counter nut to be used: SKINTOP® GMP-GL

Remark

Photographs are not to scale and do not represent detailed images of the respective products.



Technical Data

Caution:	Refer to Appendix T21 for the installation dimensions and torques
Colour delivered:	Silver grey (RAL 7001) Light grey (RAL 7035) Black (RAL 9005), UV-resistant
Material:	Body: Polyamide Seal: CR
Tests:	GGVS: TÜ.EGG.020-95
Protection rating:	Outdoors
Temperature range:	-20°C to +80°C

Product Management	Document: LAPP_PRO1067EN.pdf	1 / 4
--------------------	------------------------------	-------




SKINTOP® STR


12.09.2012

Part number	Article designation / size	Clamping range ØF (mm)	SW (mm)	Overall length/ C (mm)	Thread length inner mm	Pieces / PU
SKINTOP® STR silver grey						
53015100	STR 7	1,5 - 5	15	32.0	8.0	100
53015110	STR 9	2 - 6	19	36.0	8.0	100
53015120	STR 11	2 - 7	22	38.0	8.0	100
53015130	STR 13,5	4 - 9	24	41.0	9.0	100
53015140	STR 16	6 - 12	27	44.0	10.0	50
53015150	STR 21	9 - 16	33	49.0	11.0	50
53015160	STR 29	11 - 20	42	56.0	11.0	25
53015170	STR 36	17 - 26	53	66.0	13.0	10
53015180	STR 42	22 - 31	60	68.0	13.0	5
53015190	STR 48	26 - 35	65	69.0	14.0	5
SKINTOP® STR black						
53015300	STR 7	1,5 - 5	15	32.0	8.0	100
53015310	STR 9	2 - 6	19	36.0	8.0	100
53015320	STR 11	2 - 7	22	38.0	8.0	100
53015330	STR 13,5	4 - 9	24	41.0	9.0	100
53015340	STR 16	6 - 12	27	44.0	10.0	50
53015350	STR 21	9 - 16	33	49.0	11.0	50
53015360	STR 29	11 - 20	42	56.0	11.0	25
53015370	STR 36	17 - 26	53	66.0	13.0	10
53015380	STR 42	22 - 31	60	68.0	13.0	5
53015390	STR 48	26 - 35	65	69.0	14.0	5
SKINTOP® STR light grey						
53018100	STR 7	1,5 - 5	15	32.0	8.0	100
53018110	STR 9	2 - 6	19	36.0	8.0	100
53018120	STR 11	2 - 7	22	38.0	8.0	100
53018130	STR 13,5	4 - 9	24	41.0	9.0	100
53018140	STR 16	6 - 12	27	44.0	10.0	50
53018150	STR 21	9 - 16	33	49.0	11.0	50
53018160	STR 29	11 - 20	42	56.0	11.0	25
53018170	STR 36	17 - 26	53	66.0	13.0	10



Part number	Article designation / size	Clamping range ØF (mm)	SW (mm)	Overall length/ C (mm)	Thread length inner mm	Pieces / PU
53018180	STR 42	22 - 31	60	68.0	13.0	5
53018190	STR 48	26 - 35	65	69.0	14.0	5

U.I. Lapp GmbH	PRODUCT INFORMATION	 LAPP GROUP
SKINTOP® STR		12.09.2012



Product Management	Document: LAPP_PRO1067EN.pdf	4 / 4
--------------------	------------------------------	-------