


Inductive sensor Bi1,5-G08-AN7X


TURCK

Industrial
Automation



- Threaded barrel, M8 x 1
- Stainless steel, 1.4404
- 3-wire DC, 10...30 VDC
- normally open npn output
- TTL compatible
- cable connection

Wiring diagram



Functional principle




Inductive sensors detect metal objects contactless and wear-free. For this purpose they use a high-frequency electromagnetic AC field that interacts with the target. The sensors hosting a ferrite core coil generate the AC field through an LC resonant circuit.

Type	Bi1,5-G08-AN7X
Ident-No.	4701125
Rated operating distance Sn	1.5 mm
Mounting condition	flush
Assured sensing range	$\leq (0,81 \times S_n)$ mm
Correction factors	St37 = 1, V2A ~ 0.7, Ms ~ 0.4, Al ~ 0.3
Repeatability	$\leq 2\%$
Temperature drift	$\leq \pm 10\%$
Hysteresis	3... 15 %
Ambient temperature	-25...+ 70 °C
Operating voltage	10... 30 VDC
Residual ripple	$\leq 10\% U_{ss}$
DC rated operational current	≤ 150 mA
No-load current I_0	≤ 10 mA
Residual current	≤ 0.1 mA
Rated insulation voltage	≤ 0.5 kV
Short-circuit protection	no
Voltage drop at I_e	≤ 0.7 V
Wire breakage / Reverse polarity protection	yes / yes (voltage supply)
Output function	3-wire, NO contact, NPN
Switching frequency	≤ 3 kHz
Housing	threaded barrel, M8 x 1
Dimensions	56.6 mm
Housing material	Metal, V2A (1.4301)
Material active face	Plastic, plastic, PA12-GF20
End cap	Plastic, PP
Tightening torque of housing nut	10 Nm
Electrical connection	cables
Cable quality	$\varnothing 4$, LifYY-11Y, PUR, 2 m
Cable cross section:	$3 \times 0.25\text{mm}^2$
Vibration resistance	55 Hz (1 mm)
Shock resistance	30g (11 ms)
Protection class	IP67
Switching state	LED yellow

**Inductive sensor
Bi1,5-G08-AN7X**

Mounting instructions	minimum distances
Distance D	2 x B
Distance W	3 x Sn
Distance T	3 x B
Distance S	1.5 x B
Distance G	6 x Sn

Diameter of the active area B \varnothing 8 mm





Inductive sensor Bi1,5-G08-AN7X

TURCK

Industrial
Automation

Accessories

Type code	Ident-No.	Short text	Dimension drawing
BST-08B	6947210	Fixing clamp with dead-stop; material: PA6	
MW-08	6945008	Mounting bracket; material: Stainless steel A2 1.4301 (AISI 304)	
BSS-08	6901322	Fixing clamp; material: Polypropylene	