

# BNC Isolated Bulkhead Jack Receptacle



**RoHS  
Compliant**



## Specifications:




Frequency Range : DC-4GHz  
 Nominal Impedance : 50Ω  
 Working Voltage : 500V Max.  
 Proof Voltage : 1,500V  
 VSWR : 1.3 Max. at 1GHz

## Materials

Bodies : Brass per JIS-C3604  
 Centre Contact : Brass per JIS-3604

## Environmental

Operating Temperature Range : -40°C to +60°C



## Mounting Hole

Dimensions : Millimetres (Inches)

## Finishes and Others:

No	Description	Material	Q'ty	Finish
1	Washer	Steel	1	Nickel
2	Nut	Brass		Nickel
3	Washer			Nickel 100µ" Min.
4	Body II			Nickel 100µ" Min.
5	Grounding Tab			Tin 120µ" Min.
6	Body I	ABS		None
7	Centre Contact	Brass		Gold

## Part Number Table

Description	Part Number
BNC Isolated Bulkhead Jack Receptacle	MCCX1001

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com  
 www.farnell.com  
 www.newark.com

