

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
 FREEPORT, ILLINOIS

FED. MFR. CODE 91929

SWITCH - BASIC

(M) DT-2R4-B6
 ISSUE 2

DT-2R4-B6

M

DRAWING NUMBER

9

8

ISSUE

8

REPLACES

RELEASE NO.

CHECK

CHECK

CHECK


28 JUN 61

DRAWN

L S D


REVISIONS

A	CO15451	L S D	28 JUN 61
B	CO17707	R E R	14 MAR 63
C	CO17725	L S D	25 JUN 63
D	CO19276	M B F	12 JUNE 64
E	CO-30659	S R H	31 MAY 72
F	CO37528	C J H	31 AUG 76
G	CO 39046	G A S	16 SEPT 77



NOTE -
 ▲ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF
 .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE ----- 12-20 OZ	CONTACT ARRANGEMENT D. P. D T	DO NOT SCALE PRINT
RELEASE FORCE ----- 1 OZ MIN	UNDERWRITERS' LAB. INC. LISTED RATING -L59- 10 A-125 OR 250 VAC 0.3 A-125 VDC ; 0.15 A-250 VDC	UNLESS OTHERWISE SPECIFIED
DIFFERENTIAL TRAVEL ----- .040-.060		DIMENSIONS ARE IN INCHES TOLERANCES ARE: ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.008 ANGLES ±
OVERTRAVEL ----- .015 MIN		WEIGHT