

SAIB-M23-12P-AN-5,0M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

The M23 cables offer: high mating frequency, high current carrying capacity and high-density contacts coupled with minimal dimensions.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

General ordering data

Type	SAIB-M23-12P-AN-5,0M
Order No.	1877440500
Version	Sensor/actuator line, One end without connector, M23, No. of poles: 12, 5 m, bush, 90°, shielded: No, LED: No, Sheath material: PUR, Halogen: No
GTIN (EAN)	4032248498352
Qty.	1 pc(s).

SAIB-M23-12P-AN-5,0M
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data
Dimensions and weights

Net weight	999 g
------------	-------

Technical specifications for cable

No. of poles	12	Wire cross section	3 x 0.75 mm ² + 8 x 0.34 mm ²
shielded	No	Insulation	TPM
Colour coding	White, Green, Yellow, Grey, Pink, Red, Black, Violet, Blue, Brown, green / yellow	Sheath material	PUR
Sheathing colour	Black	Outer diameter	7.7 ± 0.3 mm
Cable length	5 m	Temperature range, moving, min.	-5 °C
Temperature range, moving, max.	80 °C	Temperature range, stationary, min.	-40 °C
Temperature range, stationary, max.	80 °C	Halogen	No
Suitable for cable carriers	Yes	Torsion resistance	0 °/m
Bending radius, min., moving	10 x cable diameter	Bending cycles	2 Mio
Resistant to welding beads	No		

General technical data

Version	bush, 90°	Contact tube diameter	M23
Housing main material	PUR	Threaded ring material	Diecast zinc
Protection degree	IP 67	Contact surface	Gold-plated
LED	No	Rated voltage	150 V
Rated current	8 A	Insulation resistance	10 ¹² Ω
Temperature range of housing	-40...+125 °C	Tightening torque	M23: 2.5 Nm
Pollution severity	2	jumpered	No

Classifications

ETIM 2.0	EC000304	ETIM 3.0	EC001855
UNSPSC	26-12-16-13	eClass 4.1	27-06-00-00
eClass 5.1	27-06-91-90	eClass 6.2	27-06-91-90
eClass 7.1	27-06-91-90		

Approvals

Approvals	
ROHS	Conform

Data sheet...

SAIB-M23-12P-AN-5,0M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

