



Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 11

Loctite 574

sds no. : 153497
V003.2

Revision: 13.09.2013
printing date: 18.10.2013

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Loctite 574

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Anaerobic Sealant

1.3. Details of the supplier of the safety data sheet

Henkel Limited

2 Bishop Square Business Park

AL109EY Herfordshire Hatfield

Great Britain

Phone: +44 1606 593933

Fax-no.: +44 1606 863762

ua-productsafety.uk@uk.henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (DPD):

Sensitizing

R43 May cause sensitisation by skin contact.

Dangerous for the environment

R52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

2.2. Label elements

Label elements (DPD):

|| Xi - Irritant



Risk phrases:

|| R43 May cause sensitisation by skin contact.
|| R52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Safety phrases:

|| S23 Do not breathe vapour.
|| S24/25 Avoid contact with skin and eyes.
|| S37 Wear suitable gloves.
|| S51 Use only in well-ventilated areas.
|| S61 Avoid release to the environment. Refer to special instructions/Safety data sheets.

Additional labeling:

For consumer use only: S2 Keep out of the reach of children
S46 If swallowed, seek medical advice immediately and show this container or label.

Contains:

Maleic acid

2.3. Other hazards

None if used properly.

SECTION 3: Composition/information on ingredients

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Decan-1-ol 112-30-1	203-956-9	5- 10 %	Serious eye irritation 2 H319 Chronic hazards to the aquatic environment 2 H411
Cumene hydroperoxide 80-15-9	201-254-7	0,1- 1 %	Organic peroxides E H242 Acute toxicity 3; Inhalation H331 Acute toxicity 4; Dermal H312 Acute toxicity 4; Oral H302 Specific target organ toxicity - repeated exposure 2 H373 Chronic hazards to the aquatic environment 2 H411 Skin corrosion 1B H314
Maleic acid 110-16-7	203-742-5 01-2119488705-25	0,1- 1 %	Acute toxicity 4; Oral H302 Acute toxicity 4; Dermal H312 Skin irritation 2 H315 Skin sensitizer 1 H317 Serious eye irritation 2 H319 Specific target organ toxicity - single exposure 3 H335
1,4-Naphthalenedione 130-15-4	204-977-6	>= 0,01 - < 0,1 %	Acute toxicity 3; Oral H301 Skin irritation 2; Dermal H315 Skin sensitizer 1; Dermal H317 Serious eye irritation 2 H319 Acute toxicity 1; Inhalation H330 Specific target organ toxicity - single exposure 3; Inhalation H335 Acute hazards to the aquatic environment H400 Chronic hazards to the aquatic environment H410

For full text of the H - statements and other abbreviations see section 16 "Other information".
Substances without classification may have community workplace exposure limits available.

Declaration of ingredients according to DPD (EC) No 1999/45:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Decan-1-ol 112-30-1	203-956-9	5 - 10 %	N - Dangerous for the environment; R51/53 Xi - Irritant; R36
Cumene hydroperoxide 80-15-9	201-254-7	0,1 - 1 %	T - Toxic; R23 Xn - Harmful; R21/22, R48/20/22 O - Oxidizing; R7 C - Corrosive; R34 N - Dangerous for the environment; R51/53
Maleic acid 110-16-7	203-742-5 01-2119488705-25	0,1 - 1 %	Xn - Harmful; R21/22 Xi - Irritant; R36/37/38, R43
1,4-Naphthalenedione 130-15-4	204-977-6	>= 0,01 - < 0,1 %	T+ - Very toxic; R25, R26 Xi - Irritant; R36/37/38, R43 N - Dangerous for the environment; R50/53

For full text of the R-Phrases indicated by codes see section 16 'Other Information'.

Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.
Seek medical advice.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

Ingestion:

Rinse out mouth, drink 1-2 glasses of water, do not induce vomiting.
Seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

SKIN: Rash, Urticaria.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

Carbon dioxide, foam, powder

Extinguishing media which must not be used for safety reasons:

None known

5.2. Special hazards arising from the substance or mixture

Do not expose to direct heat.
Oxides of carbon, oxides of nitrogen, irritating organic vapors.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Avoid skin and eye contact.
Ensure adequate ventilation.

6.2. Environmental precautions

Do not let product enter drains.

6.3. Methods and material for containment and cleaning up

For small spills wipe up with paper towel and place in container for disposal.
For large spills absorb onto inert absorbent material and place in sealed container for disposal.
Dispose of contaminated material as waste according to Chapter 13.

6.4. Reference to other sections

See advice in chapter 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Use only in well-ventilated areas.

Prolonged or repeated skin contact should be avoided to minimise any risk of sensitisation.

Hygiene measures:

Good industrial hygiene practices should be observed.

Do not eat, drink or smoke while working.

Wash hands before work breaks and after finishing work.

7.2. Conditions for safe storage, including any incompatibilities

Store in original containers at 8-21°C (46.4-69.8°F) and do not return residual materials to containers as contamination may reduce the shelf life of the bulk product.

7.3. Specific end use(s)

Anaerobic Sealant

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for

Great Britain

None

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Maleic acid 110-16-7	aqua (freshwater)					0,074 mg/L	
Maleic acid 110-16-7	aqua (intermittent releases)					0,744 mg/L	
Maleic acid 110-16-7	sediment (freshwater)				0,0624 mg/kg		
Maleic acid 110-16-7	STP					3,33 mg/L	

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Maleic acid 110-16-7	worker	Dermal	Acute/short term exposure - local effects		0,55 mg/cm ²	
Maleic acid 110-16-7	worker	Dermal	Long term exposure - local effects		0,04 mg/cm ²	
Maleic acid 110-16-7	worker	Dermal	Acute/short term exposure - systemic effects		58 mg/kg bw/day	
Maleic acid 110-16-7	worker	Dermal	Long term exposure - systemic effects		3,3 mg/kg bw/day	

Biological Exposure Indices:

None

8.2. Exposure controls:

Respiratory protection:

Use only in well-ventilated areas.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Wear protective glasses.

Skin protection:

Wear suitable protective clothing.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	paste orange
Odor	Mild
Odour threshold	No data available / Not applicable
pH	not applicable
Initial boiling point	> 150 °C (> 302 °F)
Flash point	> 100 °C (> 212 °F)
Decomposition temperature	No data available / Not applicable
Vapour pressure (27,0 °C (80.6 °F))	6,6700000 mbar
Density (ρ)	1,15 g/cm ³
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative) (Solvent: Water)	Slight
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

Ignition temperature

Not available.

SECTION 10: Stability and reactivity**10.1. Reactivity**

Reaction with strong acids.
Reacts with strong oxidants.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

Stable

10.5. Incompatible materials

No data available.

10.6. Hazardous decomposition products

Irritating organic vapours.

SECTION 11: Toxicological information**11.1. Information on toxicological effects****General toxicological information:**

The preparation is classified based on the conventional method outlined in Article 6(1)(a) of Directive 1999/45/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Oral toxicity:

This material is considered to have low toxicity if swallowed.

Inhalative toxicity:

Inhalation of vapors in high concentration may cause irritation of respiratory system

Skin irritation:

May cause sensitization by skin contact.

Acute oral toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Decan-1-ol 112-30-1	LD50	> 5.000 mg/kg	oral		rat	
Cumene hydroperoxide 80-15-9	LD50	550 mg/kg	oral		rat	

Acute inhalative toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Decan-1-ol 112-30-1	LC50	4 mg/l	inhalation	2 h	mouse	

Skin corrosion/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Decan-1-ol 112-30-1	moderately irritating	4 h	rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)
Decan-1-ol 112-30-1	slightly irritating	4 h	human	
Cumene hydroperoxide 80-15-9	corrosive		rabbit	

Serious eye damage/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Decan-1-ol 112-30-1	highly irritating		rabbit	
Decan-1-ol 112-30-1	highly irritating		rabbit	

Germ cell mutagenicity:

Hazardous components CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Decan-1-ol 112-30-1	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		
Cumene hydroperoxide 80-15-9	positive	bacterial reverse mutation assay (e.g Ames test)	without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Cumene hydroperoxide 80-15-9	negative	dermal		mouse	

SECTION 12: Ecological information**General ecological information:**

Cured Loctite products are typical polymers and do not pose any immediate environmental hazards.

The preparation is classified based on the conventional method outlined in Article 6(1)(a) of Directive 1999/45/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

12.1. Toxicity**Ecotoxicity:**

Do not empty into drains / surface water / ground water.

Harmful to aquatic organisms.

May cause long-term adverse effects in the aquatic environment.

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
Decan-1-ol 112-30-1	LC50	2,2 - 2,5 mg/l	Fish	96 h	Pimephales promelas	OECD Guideline 203 (Fish, Acute Toxicity Test)
Decan-1-ol 112-30-1	EC50	2,9 mg/l	Daphnia	48 h	Daphnia magna	
Decan-1-ol 112-30-1	EC50	2,9 mg/l	Daphnia	48 h	Daphnia magna	
Decan-1-ol 112-30-1	EC50	4,4 mg/l	Algae	5 d	Chlorella vulgaris	OECD Guideline 201 (Alga, Growth Inhibition Test)
Cumene hydroperoxide 80-15-9	LC50	3,9 mg/l	Fish	96 h	Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute Toxicity Test)
Cumene hydroperoxide 80-15-9	EC50	18 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Cumene hydroperoxide 80-15-9	EC50	18 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Cumene hydroperoxide 80-15-9	ErC50	3,1 mg/l	Algae	72 h	Pseudokirchnerella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)
Maleic acid 110-16-7	LC50	> 245 mg/l	Fish	48 h	Leuciscus idus	
Maleic acid 110-16-7	EC50	245 mg/l	Daphnia	24 h	Daphnia magna	
1,4-Naphthalenedione 130-15-4	EC50	245 mg/l	Daphnia	24 h	Daphnia magna	
1,4-Naphthalenedione 130-15-4	EC50	0,011 mg/l	Algae	72 h	Dunaliella bioculata	OECD Guideline 201 (Alga, Growth Inhibition Test)

12.2. Persistence and degradability

Hazardous components CAS-No.	Result	Route of application	Degradability	Method
Decan-1-ol 112-30-1	readily biodegradable	aerobic	86 %	EU Method C.4-E (Determination of the "Ready" Biodegradability Closed Bottle Test)
Cumene hydroperoxide 80-15-9			18 %	OECD Guideline 301 E (Ready biodegradability: Modified OECD Screening Test)
Maleic acid 110-16-7	readily biodegradable	aerobic	87 - 88 %	EU Method C.4-E (Determination of the "Ready" Biodegradability Closed Bottle Test)
1,4-Naphthalenedione 130-15-4		no data	0 - 60 %	

12.3. Bioaccumulative potential / 12.4. Mobility in soil

Hazardous components CAS-No.	LogKow	Bioconcentration factor (BCF)	Exposure time	Species	Temperature	Method
Decan-1-ol 112-30-1	4,57					
Cumene hydroperoxide 80-15-9		9,1		calculation		OECD Guideline 305 (Bioconcentration: Flow- through Fish Test)
Cumene hydroperoxide 80-15-9	2,16					
Maleic acid 110-16-7	-0,48					
1,4-Naphthalenedione 130-15-4	1,71					

12.5. Results of PBT and vPvB assessment

Hazardous components CAS-No.	PBT/vPvB
Maleic acid 110-16-7	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

Dispose of in accordance with local and national regulations.

Contribution of this product to waste is very insignificant in comparison to article in which it is used

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Waste code

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

SECTION 14: Transport information

14.1. UN number

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.4. Packaging group

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.5. Environmental hazards

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.6. Special precautions for user

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content < 5 %
(1999/13/EC)

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

- R21/22 Harmful in contact with skin and if swallowed.
- R23 Toxic by inhalation.
- R25 Toxic if swallowed.
- R26 Very toxic by inhalation.
- R34 Causes burns.
- R36 Irritating to eyes.
- R36/37/38 Irritating to eyes, respiratory system and skin.
- R43 May cause sensitisation by skin contact.
- R48/20/22 Harmful: danger of serious damage to health by prolonged exposure through inhalation and if swallowed.
- R50/53 Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
- R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
- R7 May cause fire.
- H242 Heating may cause a fire.
- H301 Toxic if swallowed.
- H302 Harmful if swallowed.
- H312 Harmful in contact with skin.
- H314 Causes severe skin burns and eye damage.
- H315 Causes skin irritation.
- H317 May cause an allergic skin reaction.
- H319 Causes serious eye irritation.
- H330 Fatal if inhaled.
- H331 Toxic if inhaled.
- H335 May cause respiratory irritation.
- H373 May cause damage to organs through prolonged or repeated exposure.
- H400 Very toxic to aquatic life.
- H410 Very toxic to aquatic life with long lasting effects.
- H411 Toxic to aquatic life with long lasting effects.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.