

Snap-in markers - US-EMP (29X8) - 0829436

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Snap-in markers, Card, white, Unlabeled, Can be labeled with: THERMOMARK CARD PLUS, THERMOMARK CARD, Mounting type: Snapped into marker carrier, Lettering field: 29 x 8 mm




The illustration shows a version of the product

Why buy this product

- The US-EMP ... UniSheet labeling range includes markers that can be fitted into existing CARRIER EMP ... label frames
- The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- The perforated markers are easy to separate and can be easily fitted
- The sheets provide space for including function texts

Key commercial data

Packing unit	10 PCE
Minimum order quantity	10 PCE
GTIN	 4 046356 562232
Weight per Piece (excluding packing)	9.77 GRM
Weight per piece (including packing)	9.77 GRM
Custom tariff number	39204910
Country of origin	Germany
Sales Key	B1 - Marking Assembly

Technical data

Dimensions

Length (b)	29 mm
Height	0.5 mm
Width (a)	8 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-30 °C ... 80 °C
Ambient temperature (assembly)	15 °C ... 25 °C

General

Color	white
-------	-------

Snap-in markers - US-EMP (29X8) - 0829436

Technical data

General

Inflammability class according to UL 94	V0
Components	Silicone-free
Material	PVC
	PVC
Number of individual labels	48
Number of individual labels per row	3
RoHS compliant	Yes
Halogen-free	No
Silicone-free	Yes
Cadmium-free	Yes
File number	U9
Printability	Thermal transfer
Device	5146464 THERMOMARK CARD
	5146451 THERMOMARK CARD-US-MAG1
Ink ribbon	0801371 THERMOMARK-RIBBON 110-TC
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:1997-06
Climate level	KFW 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	IEC 61010-1:2010-06
Result	Test passed
Burning behaviour	self-extinguishing
Foil strength	500 µm

Classifications

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001694
ETIM 5.0	EC001694

UNSPSC

UNSPSC 11	39121410
UNSPSC 12.01	39121410

Snap-in markers - US-EMP (29X8) - 0829436

Classifications

UNSPSC

UNSPSC 13.2	39121410
UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

Accessories

Accessories

Magazine - THERMOMARK CARD-US-MAG1 - 5146451



Magazine for the THERMOMARK CARD printer, for accommodating US cards