

RJS

7 2 2


V @

° †

o



Φ22mm diameter  
 Switch Rating: 7A/472VCC  
 Contact Configuration: 1NO3PE  
 Operation Type: Momentary  
 The Front Shape: Flat Head  
 The Surface Material: BS/SS/B/BLK  
 IP Degree: IP65



**RJS105-44-F-(BS/SS/B/BLK)-IP65**

RJS105 = Single Pole Type 5 Series

22 = Diameter (in mm)

F = Flat Head

BS/SS/B/BLK = Brushed Steel / Shiny Steel / Brass / Black (Surface Finish)

IP65 = IP Degree, IP 65 Standard

<b>Specification</b>	<b>RJS325/44/H/X/RR87</b>	
<b>The Front Shape</b>	Flat Head	
<b>Terminal Type</b>	5 Terminals	
<b>Switching</b>	1NO3PE	
<b>Max. Switch Rating</b>	7A/472VAC	
<b>Contact Resistance</b>	≤50mΩ	
<b>Insulation Resistance</b>	≥1000MΩ	
<b>Dielectric Intensity</b>	2000VAC	
<b>Operating Temp</b>	-20°C ~ +55°C	
<b>Mechanical Life</b>	1,000,000cycles	
<b>Electrical Life</b>	70,000cycles	
<b>Panel Thickness</b>	1~6mm	
<b>Torque</b>	5~14Nm	
<b>Operation Pressure</b>	About 70N	
<b>Operation Distance</b>	About 4.5mm	
<b>IP Degree</b>	IP65	
<b>Material</b>	<b>Contact</b>	Silver Alloy
	<b>Button</b>	BS/SS/B/BLK
	<b>Body</b>	BS/SS/B/BLK
	<b>Base</b>	PC
	<b>ROHS</b>	Made to order