



## SMA BULKHEAD RECEPTACLES – female contacts

| Description               | Terminal Type | Plt. | Ins. | Construction Notes                          |             | Dim Inches (mm) |           | Amphenol Number              | Fig. |
|---------------------------|---------------|------|------|---|-------------|-----------------|-----------|------------------------------|------|
|                           |               |      |      |   |             | a               | d         |                              |      |
| Rear Mount/<br>Hex Flange | Solder Cup    | P10  | D1   | Captive Contact/<br>.066(1.7mm) Exposed TFE | Gold Plated | .668(17.0)      | .066(1.7) | <a href="#">901-9211</a>     | 1    |
|                           | Solder Cup    | P13  | D1   |   | Passivated  | .668(17.0)      | .066(1.7) | <a href="#">901-9211-SF</a>  | 1    |
| Front or<br>Rear Mount    | Blunt Post    | P10  | D1   | Captive Contact/<br>.076(1.9mm) Exposed TFE | Gold Plated | .660(16.7)      | .076(1.9) | <a href="#">901-9220</a>     | 2    |
|                           | Blunt Post    | P13  | D1   |   | Passivated  | .660(16.7)      | .076(1.9) | <a href="#">901-9220-SF</a>  | 2    |
|                           | Blunt Post    | P11  | D1   | Captive Contact/Flush TFE                   | Gold Plated | .625(15.9)      | .076(1.9) | <a href="#">901-9835</a>     | 2    |
| Front Mount               | Post          | P11  | D1   | Flush TFE                                   | Gold Plated | .400(10.2)      | —         | <a href="#">901-9841</a>     | 3    |
| Rear Mount<br>Hex. Flange | Solder Cup    | P10  | D1   | Mechanically captivated                     | Gold Plated | .668(17.0)      | .066(1.7) | <a href="#">901-10032</a>    | 1    |
|                           | Solder Cup    | P13  | D1   | Mechanically captivated                     | Passivated  | .668(17.0)      | .066(1.7) | <a href="#">901-10032-SF</a> | 1    |