





## Products

### LED Indicators

CML IT offers panel mount indicators manufactured with LED, Neon or Incandescent light sources. These indicators are available in a number of different lens and termination styles, with voltages of 2V - 250V available off-the-shelf.



**Part Number:** 19091350  
**Serial Number:** 1905  
**Mounting hole (inch):** 0.3150"  
**Mounting hole (metric):** 8mm  
**Indicator type:** sunlight visibility  
**Mounting type:** with bezel  
**Bezel type:** recessed  
**Bezel material:** metal  
**Bezel color:** black chrome  
**Bezel size:** M8  
**Protection:** IP67  
**Lens type:** round  
**Lens color:** red diffused  
**Lens size:** 5mm  
**Connector tpe:** tab terminals 2.8x0.8mm  
**Connector number:** 2  
**Connector for lamp test:** no  
**Number LED chip:** 1  
**Indicator color:** red  
**Dom wave length:** 640nm  
**Peak wave length (mA):**  
**Op. voltage (V):** 24V AC/DC  
**Forward volt max:**  
**Rectifier:** Half Wave  
**AC current:** 9mA  
**DC current:** 17mA  
**Lum in min (mcd):**  
**Lum in type (DC):** 1200mcd  
**Voltage type (%):** 10%  
**Op. temperature (°C):** -25 °C - +60 °C  
**Storage temperature (°C):** -25 °C - +60 °C  
**Narrative:**  
**Viewing angle (°):**  
**RoHS Status:** Yes



Alle Maße in mm / All dimensions are in mm

Elektrische und optische Daten sind bei einer Umgebungstemperatur von 25°C gemessen.  
Electrical and optical data are measured at an ambient temperature of 25°C.

Bestell-Nr. Part No.	Farbe Colour	Spannung Voltage	Strom Current	Lichtstärke Lumi. Intensity
1909x350	Red	24V AC/DC	9/17mA	1200mcd
1909x355	Green	24V AC/DC	9/17mA	1300mcd
1909x352	Yellow	24V AC/DC	9/17mA	1100mcd
1909x357	Blue	24V AC/DC	9/17mA	600mcd
1909x35W	White	24V AC/DC	9/17mA	1000mcd

Lichtstärkedaten der verwendeten Leuchtdioden bei DC / Luminous intensity data of the used LEDs at DC

Lagertemperatur / Storage temperature -25°C - +80°C  
Umgebungstemperatur / Ambient temperature -20°C - +60°C  
Spannungstoleranz / Voltage tolerance +10%

Schutzart: IP67 nach DIN EN 60529 - Frontseitig zwischen LED und Gehäuse, sowie zwischen Gehäuse und Frontplatte bei Verwendung des mitgelieferten Dichtringes.  
Degree of protection: IP67 in accordance with DIN EN 60529 - Gap between LED and bezel and gap between bezel and frontplate sealed to IP67 when using the supplied gasket.

x = 0 glanzverchromter Metallreflektor / satin chrome bezel  
x = 1 schwarzverchromter Metallreflektor / black chrome bezel  
x = 2 mattverchromter Metallreflektor / matt chrome bezel

**Allgemeiner Hinweis:** Bedingt durch die Fertigungstoleranzen der Leuchtdioden kann es zu geringfügigen Schwankungen der Farbe (Farbtemperatur) kommen. Es kann deshalb nicht ausgeschlossen werden, daß die Farben der Leuchtdioden eines Fertigungsloses unterschiedlich wahrgenommen werden.

**General:** Due to production tolerances, colour temperature variations may be detected within individual consignments.

Die Anzeigen mit Flachsteckeranschlüssen sind nicht für Lötanschluss geeignet / The indicators with tabconnection are not qualified for soldering.

Der Kunststoff (Polycarbonat) ist nur bedingt chemikalienbeständig / The plastic (polycarbonate) is limited resistant against chemicals.

Die Auswahl und der technisch richtige Einbau unserer Produkte, nach den entsprechenden Vorschriften (z.B. VDE 0100 und 0160), obliegen dem Anwender / The selection and technical correct installation of our products, conforming for the relevant standards (e.g. VDE 0100 and VDE 0160) is incumbent on the user.



**LED Indicator 8mm  
Recessed (Interior) Bezel Sunlight Visibility**

Drawn: **J.J.** Ch'd: **D.L.** Date: **10.01.06**

Revision: Date: Name: Scale: **2 : 1** Datasheet: **1909x35x**