



A highly flexible, low cost package for RF applications in the 1-30MHz band. The use of vacuum reed switches with rhodium contacts offers high isolation voltages, low contact resistance and long operating lifetime. Additional RF screening is available to further enhance RF performance for more demanding applications.

- **3.5A RF at 1-30MHz**
- **3.5kV Isolation**
- **Contacts Form A, B or Latching**
- **Long Lifetime**

Available as Form A (SPNO), Form B (SPNC) or latching (bistable) contact configurations with switch connections via either PCB or flying lead.

Contact	Units	Conditions	Form A	Form B	Latching
Contact Material			Rhodium	Rhodium	Rhodium
Isolation across contacts	kV	DC or AC peak	3	3	3.5
Max. carry current	A	DC or AC rms	3.5*	3.5*	1.5
Max. switching power	W		10	10	10
Max. switching voltage	V	DC or AC peak	20	20	20
Max. switching current	A	DC or AC peak	0.5	0.5	0.5
Capacitance across contacts	pF	coil/screen grounded	<0.1	<0.1	<0.1
Lifetime	operations	dry switching	10 <sup>9</sup>	10 <sup>9</sup>	10 <sup>9</sup>
Lifetime	operations	10W switching	10 <sup>8</sup>	10 <sup>8</sup>	10 <sup>8</sup>
Contact Resistance	mOhms	maximum (typical)	80 (30)	80 (30)	80 (30)
Insulation Resistance	Ohms	minimum (typical)	10 <sup>10</sup> (10 <sup>13</sup> )	10 <sup>10</sup> (10 <sup>13</sup> )	10 <sup>10</sup> (10 <sup>13</sup> )
ESR at 30MHz (no screen)	mOhms	typical	95 @ 3A rms	95 @ 3A rms	200 @ 1.5A rms
ESR at 30MHz (part screen)	mOhms	typical	80 @ 3A rms	80 @ 3A rms	180 @ 1.5A rms
<b>Coil</b>			<b>5V 12V 24V</b>	<b>5V 12V 24V</b>	<b>5V 12V</b>
Must Operate	V	DC, 20°C	3.5 8 15	3.5 8 15	3 7
Must Release	V	DC, 20°C	1 2 4	1 2 4	N/A N/A
Min Pulse Length	ms		N/A N/A N/A	N/A N/A N/A	2.0 2.0
Operate Time	ms		1.0 1.0 1.0	1.0 1.0 1.0	1.0 1.0
Release Time	ms	diode fitted	0.5 0.5 0.5	0.5 0.5 0.5	1.0 1.0
Resistance	Ohms	20°C	70 380 1500	65 350 1200	188 500
<b>Construction</b>					
Isolation contact to coil	kV	DC or AC peak	3	3	3.5
Capacitance contact to all other terminals	pF	Contacts open	<1.0	<1.0	<1.0
Capacitance contact to all other terminals	pF	Contacts closed	<1.5	<1.5	<1.5
<b>Environmental</b>					
Operating temperature range	°C	Limited Current	-40 to +100*	-40 to +100*	-40 to +100
Storage temperature range	°C		-40 to +125	-40 to +125	-40 to +125
Weight	gm	typical	3.5	4.2	3.1


\*see graphical data



**Mechanical Dimensions**


All dimensions are in millimeters (inches)

**Flying Lead**




Pins 1, 2, 5, 6 require 0.9mm diameter ± 0.05mm holes


**PCB Mount**




**Circuit Diagram, Form A**



**Circuit Diagram, Form B**



**Circuit Diagram, Latching**



(all circuit diagrams viewed from above)

**ISO9001 Certified**

**USA**  
 Sales & Tech Support(866) 258-5057  
 Email: sales@cynergy3.com  
 Cynergy3 Components  
 2320 Paseo de las Americas, Suite 104  
 San Diego, CA 92154

**EUROPE - UK**  
 Telephone +44 (0) 1202 897969  
 Fax +44 (0) 1202 891918  
 Email:sales@cynergy3.com  
 Cynergy3 Components Ltd.  
 7 Cobham Road  
 Ferndown Industrial Estate  
 Wimborne, Dorset BH21 7PE

**ASIA - Thailand**  
 Telephone +66 (0)2 665 2517  
 Fax +66 (0)2 665 2588  
 Cynergy 3 Components, Asia  
 18/8 Fico Place 12th Floor  
 Soi Sukhumvit 21 (Asoke)  
 Klongtoey Nua, Wattana  
 Bangkok, Thailand 10110