

Productname : AMBERCLENS  
Ref.Nr.: UDS000360\_3\_20131017

Creationdate : 17.10.13 Version : 1.0  
Replaces: UK10001

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

**AMBERCLENS**  
Aerosol

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Cleaners - Heavy duty

### 1.3. Details of the supplier of the safety data sheet

CRC Industries UK Ltd.  
Ambersil House - Wylds Road  
Castlefield Industrial Estate  
TA6 4DD Bridgwater Somerset  
United Kingdom  
Tel.: +44 1278 727200  
Fax.: +44 1278 425644  
E-mail : hse.uk@crcind.com

### 1.4. Emergency telephone number

(+44)(0)1278 72 7200

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

#### Classification according to 67/548/EEC or 1999/45/EC:

EXTREMELY FLAMMABLE

<b>Health:</b>	Not classified
<b>Physical:</b>	R12: Extremely flammable. EXTREMELY FLAMMABLE
<b>Environment:</b>	Not classified

### 2.2. Label elements

Warning symbol(s) : EXTREMELY FLAMMABLE



Risk-phrase(s) : R12: Extremely flammable.



Productname : AMBERCLENS  
Ref.Nr.: UDS000360\_3\_20131017

Creationdate : 17.10.13 Version : 1.0  
Replaces: UK10001

Kerosine - unspecified	43	47-8	141-6)				
------------------------	----	------	--------	--	--	--	--

**Explanation notes**

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

(\* Explanation phrases : see chapter 16)

**SECTION 4: First aid measures****4.1. Description of first aid measures**

<b>Contact with eyes :</b>	If substance has got into eyes, immediately wash out with plenty of water Seek medical attention if irritation persists
<b>Contact with skin :</b>	Wash with water and soap. Seek medical attention if irritation persists
<b>Inhalation :</b>	Fresh air, keep warm and at rest. Seek medical attention if ill effects occur
<b>Ingestion :</b>	If swallowed do not induce vomiting because of risk of aspiration into the lungs. If aspiration is suspected obtain immediate medical attention

**4.2. Most important symptoms and effects, both acute and delayed**

<b>Inhalation :</b>	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia. Symptoms : sore throat, abdominal pain, nausea, vomiting
<b>Skin contact :</b>	May cause irritation. Symptoms : redness and pain
<b>Eye contact :</b>	May cause irritation. Symptoms : redness and pain

**4.3. Indication of any immediate medical attention and special treatment needed**

<b>General Advice :</b>	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

**SECTION 5: Firefighting measures****5.1. Extinguishing media**

foam, carbon dioxide or dry agent

**5.2. Special hazards arising from the substance or mixture**

Aerosols may explode if heated above 50°C  
Forms hazardous decomposition products  
CO,CO2

**5.3. Advice for firefighters**

<b>Productname :</b>	AMBERCLENS	<b>Creationdate :</b>	17.10.13 Version : 1.0
<b>Ref.Nr.:</b>	UDS000360_3_20131017	<b>Replaces:</b>	UK10001

Keep container(s) exposed to fire cool, by spraying with water  
In case of fire, do not breathe fumes

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources  
Ensure adequate ventilation  
Wear suitable protective clothing and gloves.

### 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses  
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

### 6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

### 6.4. Reference to other sections

For further information see section 8

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Keep away from heat and sources of ignition  
Take precautionary measures against static discharges  
Equipment should be earthed  
Use explosion-proof electrical/ventilating/lighting/.../equipment.  
Use only non-sparking tools.  
Do not breathe aerosols or vapours.  
Ensure adequate ventilation  
Avoid contact with skin and eyes.  
Wash thoroughly after use  
Wear protective gloves/protective clothing/eye protection/face protection.

### 7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.  
Keep out of reach of children.

### 7.3. Specific end use(s)

Cleaners - Heavy duty

**Productname :** AMBERCLENS  
**Ref.Nr.:** UDS000360\_3\_20131017

**Creationdate :** 17.10.13 Version : 1.0  
**Replaces:** UK10001

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Exposure limits :

Hazardous ingredient	CAS-nr.	method	
<b>EU established exposure limits:</b>			
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	TWA	100 ppm
		STEL	150 ppm
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	TWA	400 ppm
		STEL	500 ppm
<b>National established exposure limits, United Kingdom</b>			
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	TWA	100 ppm
		STEL	150 ppm

### 8.2. Exposure controls

<b>Control procedures :</b>	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
<b>Personal protection :</b>	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
<b>inhalation :</b>	In case of insufficient ventilation, wear suitable respiratory equipment.
<b>hands and skin :</b>	Wear suitable protective gloves against chemicals (nitrile)
<b>eyes :</b>	Wear safety goggles.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

<b>Apperance : physical state :</b>	Liquid under pressure.
<b>colour :</b>	Colourless to yellow.
<b>odour :</b>	Characteristic odor.
<b>pH :</b>	10
<b>Boiling point/range :</b>	82 °C
<b>Flash point :</b>	12 °C
<b>Evaporation rate :</b>	Not available.
<b>Explosion limits : upper limit :</b>	15 %
<b>lower limit :</b>	0.6 %
<b>Vapour pressure :</b>	Not available.
<b>Relative density :</b>	0.962 g/cm <sup>3</sup> (@ 20°C).
<b>Solubility in water :</b>	Soluble in water
<b>Auto-ignition :</b>	225 °C

Productname : AMBERCLENS  
Ref.Nr.: UDS000360\_3\_20131017

Creationdate : 17.10.13 Version : 1.0  
Replaces: UK10001

Viscosity : Not available.

## 9.2. Other information

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No hazardous reactions known if used for its intended purpose

### 10.2. Chemical stability

Stable

### 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

### 10.4. Conditions to avoid

Avoid overheating

### 10.5. Incompatible materials

Strong oxidising agent

### 10.6. Hazardous decomposition products

CO,CO2

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

**Inhalation :** Inhalation of solvent vapours may give rise to nausea, headaches and dizziness

**Ingestion :** After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.

**Skin contact :** Prolonged skin contact will result in defatting of the skin, leading to irritation, and in some cases, dermatitis  
Repeated exposure may cause skin dryness or cracking.

**Eye contact :** May cause irritation.

### Toxicological data :

Hazardous ingredient	CAS-nr.	method	
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	LD50 oral rat	4016 mg/kg

**Productname :** AMBERCLENS  
**Ref.Nr.:** UDS000360\_3\_20131017

**Creationdate :** 17.10.13 Version : 1.0  
**Replaces:** UK10001

		LC50 inhal.rat	27596 mg/l
		LD50 derm.rabit	2000 mg/kg
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	> 20 mg/l
		LD50 derm.rabit	> 5000 mg/kg
Distillates (petroleum), hydrotreated light; Kerosine - unspecified	64742-47-8	LD50 oral rat	> 5000 mg/kg
		LD50 derm.rabit	> 5000 mg/kg

## SECTION 12: Ecological information

### 12.1. Toxicity

Not classified

### Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	LC50 fish	6812 mg/l
		EC50 daphnia	23300 mg/l
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	IC50 algae	> 1000 mg/l
		LC50 fish	> 1000 mg/l
		EC50 daphnia	> 1000 mg/l
Distillates (petroleum), hydrotreated light; Kerosine - unspecified	64742-47-8	IC50 algae	1000 mg/l
		LC50 fish	1000 mg/l
		EC50 daphnia	1000 mg/l

### 12.2. Persistence and degradability

No information available

### 12.3. Bioaccumulative potential

No information available

### 12.4. Mobility in soil

Soluble in water

### 12.5. Results of PBT and vPvB assessment

No information available

### 12.6. Other adverse effects

No information available

Productname : AMBERCLENS  
Ref.Nr.: UDS000360\_3\_20131017

Creationdate : 17.10.13 Version : 1.0  
Replaces: UK10001

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

**Product :** This material and its container must be disposed of in a safe way.  
Do not discharge into drains or the environment, dispose to an authorised waste collection point.

**National regulations :** Disposal should be in accordance with local, state or national legislation

## SECTION 14: Transport information

### 14.1. UN number

UN-number : 1950

### 14.2. UN proper shipping name

Proper shipping name: AEROSOLS

### 14.3. Transport hazard class(es)

Class: 2.1  
ADR/RID - Classification code: 5F

### 14.4. Packing group

Packing group: Not applicable.

### 14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No  
IMDG - Marine pollutant: No  
IATA/ICAO - Environmentally hazardous: No

### 14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)  
IMDG - Ems: F-D, S-U  
IATA/ICAO - PAX: 203  
IATA/ICAO - CAO: 203

### 14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.



Productname : AMBERCLENS  
Ref.Nr.: UDS000360\_3\_20131017

Creationdate : 17.10.13 Version : 1.0  
Replaces: UK10001

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.  
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.  
EU-directive 99/45/EC  
Regulation (EC) No 1272/2008 (CLP)  
Regulation (EC) No 1907/2006 (REACH)

### 15.2. Chemical safety assessment

No information available

## SECTION 16: Other information

\*Explanation risk-phrases: R10: Flammable.  
R11: Highly flammable.  
R12: Extremely flammable.  
R23: Toxic by inhalation.  
R36: Irritating to eyes.  
R38: Irritating to skin.  
R41: Risk of serious damage to eyes.  
R65: Harmful: may cause lung damage if swallowed.  
R66: Repeated exposure may cause skin dryness or cracking.  
R67: Vapours may cause drowsiness and dizziness.

\*Explanation hazard statements: H225 : Highly flammable liquid and vapour.  
H226 : Flammable liquid and vapour.  
H304 : May be fatal if swallowed and enters airways.  
H319 : Causes serious eye irritation.  
H336 : May cause drowsiness or dizziness.

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.