Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



8772 Multi-Conductor - Audio, Control and Instrumentation Cable



For more Information please call

1-800-Belden1



General Description:

20 AWG stranded (7x28) tinned copper conductors, conductors cabled, polyethylene insulation, overall Beldfoil® shield (100% coverage), 20 AWG stranded tinned copper drain wire, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

| # Conductors | AWG | Stranding | Conductor Material |
|--------------|-----|-----------|---------------------------|
| 3 | 20 | 7x28 | TC - Tinned Copper |

Total Number of Conductors: 3

Insulation

Insulation Material:

| Insulation Material | Wall Thickness (in.) |
|---------------------|----------------------|
| PE - Polyethylene | 0.017 |

Outer Shield

Outer Shield Material:

| Outer Shield Trade Name Ty | | Outer Shield Material | Coverage (%) |
|----------------------------|------|------------------------------|--------------|
| Beldfoil® (Z-Fold®) | Таре | Aluminum Foil-Polyester Tape | 100 |

Outer Shield Drain Wire AWG:

| AWG | Stranding | Drain Wire Conductor Material |
|-----|-----------|--------------------------------------|
| 20 | 7x28 | TC - Tinned Copper |

Outer Jacket

Outer Jacket Material:

| Outer Jacket Material | Nom. Wall Thickness (in.) |
|--------------------------|---------------------------|
| PVC - Polyvinyl Chloride | .033 |

Overall Cable

Overall Cabling Lay Length & Direction:

| Length (in.) | Direction | Twists (twist/ft) |
|--------------|-----------|-------------------|
| 2.000 | Left Hand | 6.000 |

Overall Cabling Color Code Chart:

| Number | Color |
|--------|-------|
| 1 | Black |
| 2 | Red |
| 3 | Clear |

Overall Nominal Diameter: 0.218 in.

Mechanical Characteristics (Overall)

| Operating Temperature Range: | -20°C To +60°C |
|-----------------------------------|--------------------------|
| UL Temperature Rating: | 60°C (UL AWM Style 2093) |
| Bulk Cable Weight: | 29 lbs/1000 ft. |
| Max. Recommended Pulling Tension: | 45 lbs. |
| Min. Bend Radius/Minor Axis: | 2.250 in. |

Page 1 of 3 10-30-2013

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION

NEC/(UL) Specification:



8772 Multi-Conductor - Audio, Control and Instrumentation Cable

| Applicable | Specifications | and Agency | Compliance | (Overall) |
|------------|----------------|---------------|------------|-----------|
| Annlinable | Ctandarda 9 En | ironmontal Dr | | |

Applicable Standards & Environmental Programs

| CEC/C(UL) Specification: C | М |
|----------------------------|---|

AWM Specification: UL Style 2093 (300 V 60°C)

EU Directive 2011/65/EU (ROHS II): Yes

CM

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: UL1685 UL Loading

CSA Flame Test: FT1

Suitability

Suitability - Indoor: Yes

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
27

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
51

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft) 10.0

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

Max. Operating Voltage - UL:

Voltage 300 V RMS

Max. Recommended Current:

Put Ups and Colors:

| Item # | Putup | Ship Weight | Color | Notes | Item Desc |
|---------------|----------|-------------|--------|-------|-----------------|
| 8772 060U1000 | 1,000 FT | 31.000 LB | CHROME | | 3 #20 PE FS PVC |
| 8772 060U500 | 500 FT | 16.000 LB | CHROME | | 3 #20 PE FS PVC |
| 8772 0601000 | 1,000 FT | 31.000 LB | CHROME | С | 3 #20 PE FS PVC |
| 8772 060500 | 500 FT | 16.000 LB | CHROME | С | 3 #20 PE FS PVC |
| 8772 0605000 | 5,000 FT | 155.000 LB | CHROME | | 3 #20 PE FS PVC |

Page 2 of 3 10-30-2013

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



8772 Multi-Conductor - Audio, Control and Instrumentation Cable

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 08-05-2013

© 2013 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.
Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.