

R2F MM Plug / R2F MM Plug Patchcord 5m



Issue

18/12/2009

Page

1/1

Dimension in mm



Cable pinout

R2F 1	R2F 2
Pin 1	Pin 1
Pin 2	Pin 2

GENERAL

Type:

End1
R2F Plug, for 2 Multimode channels.
Screw thread coupling device
(to be installed with a 100 Ncm torque
wrench).
Vinyl protective cap.

End2
R2F Plug, for 2 Multimode channels.
Screw thread coupling device
(to be installed with a 100 Ncm torque
wrench).
Vinyl protective cap.

Cable:

Field cable MM 50/125

Identification:

Self-laminated label, RADIALL / F760 888 620-05 /MO nb.

CHARACTERISTICS

(depending on cable construction)

	<i>End 1 (R2F)</i>	<i>End 2 (R2F)</i>
Optical : Cable assembly Insertion Loss (@ 850 nm) acc. to IEC 61300-3-4	1.50 dB	(method 6)
Mechanical : Endurance Tensile load Vibration	500 mating cycles up to 800 N (depending on cable) Acc. To IEC 61300.2.1	500 mating cycles up to 800 N (depending on cable) Acc. To IEC 61300.2.1
Environmental: Protection Operating temperature	IP67 (plugged) -40°C to + 85°C	IP67 (plugged) -40°C to + 85°C
2002/95/EC (RoHS)	Compliant	

CREATION

N°PEN :
Name: MM
Date: 18/12/2009
Appr.: FP

Issue	Revisions	Name	Appr.

RADIALL®

101, rue P. Hoffmann
93116 ROSNY/BOIS
FRANCE
Tel : (33) 0149353535
Fax : (33) 0148546363