


Keyboard Lead Coiled

**RoHS
Compliant**



Product Description:

Application : For communication and signal control systems
 Reference Standard : Customer's sample spec.and the general standard
 Multi-construction : 4


Cable Construction:

Conductor : Bare Copper
 Construction : 0.12 ±0.005 × 22
 Standard Dia. (±0.01mm) : 0.65
 Insulation : PVC
 Thickness : 0.36
 Insulation Dia.(±0.1mm) : 1.4
 Insulation Colour : Red, White, Brown, Blue
 Filler : Chalk
 Jacket : PVC
 Thickness (mm) : 1
 Dia. (±0.2mm) : 5.7
 Jacket Colour : Black
 Packaging : 1.65m/plastic Bag, 100 Pcs/Box
 Boxes size : 50cm × 28cm × 32cm


Electrical Characteristics:

Max.Conductor DC Resistance at 20°C (Ω/Km) : 74.8
 Min. Insulation DC Resistance at 20°C (MΩ × Km) : >500
 Rated Temperature : -20°C to +80°C
 Rated Voltage : 100V

Design



Coil size



Part Number Table

Description	Part Number
Lead, Keyboard, 4 Core, Coiled	RGW-1563