

83803 Multi-Conductor - Power-Limited Fire Protective, Control & Instrum Cable



For more Information
please call

1-800-Belden1



General Description:

12 AWG stranded (7x20) TC conductors, conductors cabled, plenum, FEP insulation, Beldfoil® (100% coverage) + TC braid shield (85% coverage), FEP jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
3	12	7x20	TC - Tinned Copper

Total Number of Conductors: 3

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Wall Thickness (mm)
Teflon®	FEP - Fluorinated Ethylene Propylene	0.4064

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100
2		Braid	TC - Tinned Copper	85

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material	Nom. Wall Thickness (mm)
Teflon®	FEP - Fluorinated Ethylene Propylene	0.381

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	White
3	Red

Overall Nominal Diameter: 8.204 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -70°C To +200°C

UL Temperature Rating: 200°C

Bulk Cable Weight: 157.749 Kg/Km

Min. Bend Radius/Minor Axis: 82.550 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMP, FPLP

NEC Articles: 760

CEC/C(UL) Specification: CMP

METRIC MEASUREMENT VERSION

83803 Multi-Conductor - Power-Limited Fire Protective, Control & Instrum Cable

EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	NFPA 262
CSA Flame Test:	FT6

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

104.992

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)

180.455

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

5.5777

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

20 Amps per conductor @ 25°C

Notes (Overall)

Notes: Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
83803 002100	30 MT	5.579 KG	RED	C	3#12 FEP SH FEP
83803 0021000	305 MT	50.349 KG	RED	C	3#12 FEP SH FEP
83803 002500	152 MT	25.628 KG	RED	C	3#12 FEP SH FEP

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 09-07-2012

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract,

METRIC MEASUREMENT VERSION

83803 Multi-Conductor - Power-Limited Fire Protective, Control & Instrum Cable

negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.