

## Black Box Products

---

Cables > Copper Patch Cables



### **GigaBase 350 CAT5e Patch Cable (UTP) with Snagless Boots, Crossover, Blue, 3-ft. (0.9-m)**

The great choice for Gigabit crossover applications

EVCRB81-0003

---

Extended Double Diamond™ Warranty Available  
(Lifetime)

#### **Product Highlights**

- Tested to 350 MHz.
- Meets or exceeds CAT5e T568B standards.
- Specially designed for use with other GigaBase components.
- Guaranteed for life!

## Details

### **Description**

GigaBase 350 CAT5e Patch Cable (UTP) with Snagless Boots, Crossover, Blue, 3-ft. (0.9-m)

### **Quick Facts**

- Tested to 350 MHz.
- Meets or exceeds CAT5e T568B standards.
- Specially designed for use with other GigaBase components.
- Guaranteed for life!

### **Further Details**

- Improved near-end crosstalk (NEXT) compared to standard CAT5 cable.
- Superior construction offers significant headroom.
- Stranded conductors for short runs.
- Tuned-plug design maintains a tighter twist and reduces noise.
- Enhanced performance parameters and electrical characteristics.
- Gold-plated contacts are designed for an insertion/extraction life of 1000 cycles.
- These patch cables have four pairs, 24 AWG construction, RJ-45 connectors, and a PVC jacket.

Use this 350-MHz cable when making switch-to-switch or other crossover connections in your CAT5e network.

## Tech Spec

Technical Specifications for GigaBase 350 CAT5e Patch Cable (UTP) with Snagless Boots, Crossover, Blue, 3-ft. (0.9-m):

<b>Attenuation (Maximum)</b>	<b>24.2 dB/100 m (328.1 ft.) at 100 MHz;</b> 49.3 dB/100 m (328.1 ft.) at 350 MHz
<b>Cable Type</b>	<b>4-pair UTP</b>
<b>Conductor Gauge</b>	<b>24 AWG, stranded</b>
<b>Frequency</b>	<b>Up to 350 MHz</b>
<b>Impedance</b>	<b>100 ± 15 ohms</b>
<b>NEXT (Minimum)</b>	<b>40.3 dB/100 m (328.1 ft.) at 100 MHz;</b> 32.2 dB/100 m (328.1 ft.) at 350 MHz
<b>PS-NEXT (Minimum)</b>	<b>38.3 dB/100 m (328.1 ft.) at 100 MHz;</b> 30.2 dB/100 m (328.1 ft.) at 350 MHz
<b>Return Loss (Minimum)</b>	<b>20.1 dB/100 m (328.1 ft.) at 100 MHz;</b> 16.3 dB/100 m (328.1 ft.) at 350 MHz
<b>Standards</b>	<b>TIA/EIA-568-B.2 Category 5e</b>

These products work with:

GigaStation High-Density Multimedia Patch Panels

GigaBase CAT5e Patch Panels

GigaBase CAT5e Jacks

GigaBase2 CAT5e Jacks

GigaStation Wallplates

GigaStation2 Wallplates

They also work with all standard jacks, wallplates, and other RJ-45 hardware.

NOTE: Technical specification weight is the unit weight. It is not the packaged shipping weight