

High Value Multilayer Ceramic Capacitors (High dielectric type)

JMK105BBJ475MV-F (Old: JMK105BJ475MV-FD)



■ Features

- Item Summary
6.3V, X5R, 4.7 μ F, $\pm$ 20%, 0402
- Lifecycle Stage
Mass Production
- Standard packaging quantity (minimum)
Taping paper 10000pcs

■ Products characteristics table

CaseSize (EIA/JIS)	0402/1005
Rated Voltage (max)	6.3V
Capacitance	4.7 μ F
Capacitance Tolerance	$\pm$ 20%
Resistance	100 M Ω μ F
Dielectric Loss Tangent	10%MAX
Temperature Characteristics (EIA/JIS)	X5R/-
Temperature Range (EIA/JIS)	-55 to +85 $^{\circ}$ C/-
Capacitance Change (EIA/JIS)	$\pm$ 15/-%
RoHS Compliance	Yes
Halogen Free	Yes
Soldering Method	Reflow

■ External Dimensions

L	1.0mm +0.15:-0.05
W	0.5mm +0.15:-0.05
T	0.5mm +0.15:-0.05
e	0.25mm $\pm$ 0.10

2013.12.16

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
 Before making final selection, please check product specification.

Multi Layer Ceramic Capacitor

TAIYO YUDEN

-Electrical Characteristics Data-






10S2C08

RoHS compliance product

○JMK105BBJ475MV

6.3V 1005 X5R 4.7 μ F $\pm$ 20% $t=0.65$ mmMAX

6.3V 0402 X5R 4.7 μ F $\pm$ 20% $t=0.026$ inchMAX



部品特性は設置環境、測定条件等により変化することがあります。本データをご使用される際は実際の製品特性に対する参考データとしてご活用ください。また、本データは予告無く追加・削除及び変更を行う場合があります。ご注文の際は、納入仕様書のご確認をお願いします。

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.

TAIYO YUDEN reserves the right to make change to the Date at any time without notice.

Before making final selection, please check product specification