



**LED**

**SPECIFICATION**

- 140 Lumen White Seoul LED
  - Industrial strength copolymer housing
  - Beammaster lens
  - Silent switch operation
  - Side charging point
  - Easy screw end cap operation
  - Carry strap, battery & charger included
  - Impact Resistant to 1M
  - Water Resistant
- 
- BATTERIES: 1×4.8v 2000 mAh rechargeable battery (Included)
  - SIZE: 135mm x 225mm
  - WEIGHT: 650g (With Battery)

ANSI FL 1	HIGH
	140 LUMENS
	3890cd
	125m
	5h
	✓
	✓

\* Flashing mode specifications cannot be measured by ANSI FL1 standard. Flashing mode runtime is based on measurement of battery capacity change only.



▶ Rechargeable Battery



▶ Mains Charger



▶ Push Button Micro switch



▶ Carry Strap