



SAFETY DATA SHEET PC-CLENE TUB 100 WIPES

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

PRODUCT NAME PC-CLENE TUB 100 WIPES
PRODUCT NO. PCC
APCC100
APCC100R
ZA
APPLICATION Office Equipment Cleaning Product
SUPPLIER AF INTERNATIONAL. A division
of HK WENTWORTH LTD
ASHBY PARK
COALFIELD WAY
ASHBY de la ZOUCH
LEICESTERSHIRE. LE65 1JF
UNITED KINGDOM
+44 (0) 1530 419600
+44 (0) 1530 416640
info@hkw.co.uk
EMERGENCY TELEPHONE +44 (0)1530 419600 between 8.30am - 5.00pm Mon – Fri

2 HAZARDS IDENTIFICATION

Not regarded as a health or environmental hazard under current legislation.

CLASSIFICATION (1999/45) Not classified.

3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content %	Classification (67/548/EEC)
1-METHOXY-2-PROPANOL	203-539-1	107-98-2	1-5%	R10 R67

The Full Text for all R-Phrases is Displayed in Section 16

COMPOSITION COMMENTS

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels

4 FIRST-AID MEASURES

NOTES TO THE PHYSICIAN

Treat symptomatically

INHALATION

Due to the small packaging the risk of inhalation is minimal.

INGESTION

Due to the small packaging the risk of ingestion is minimal. Rinse mouth thoroughly. Get medical attention.

SKIN CONTACT

Due to the small packaging the risk of skin contact is minimal. Wash the skin immediately with soap and water. Get medical attention if irritation persists after washing.

EYE CONTACT

Due to the small packaging the risk of eye contact is minimal. Rinse with water. Contact physician if discomfort continues.

5 FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

This product is not flammable. Use fire-extinguishing media appropriate for surrounding materials.

PC-CLENE TUB 100 WIPES

6 ACCIDENTAL RELEASE MEASURES

SPILL CLEAN UP METHODS

Not relevant.

7 HANDLING AND STORAGE

USAGE PRECAUTIONS

No specific usage precautions noted.

STORAGE PRECAUTIONS

Keep in original container.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
1-METHOXY-2-PROPANOL	WEL	100 ppm	375 mg/m ³	150 ppm	560 mg/m ³	Sk

WEL = Workplace Exposure Limit.
Sk = Can be absorbed through skin.

ENGINEERING MEASURES

Not relevant.

HAND PROTECTION

Hand protection not required.

EYE PROTECTION

Not relevant.

OTHER PROTECTION

Not relevant

HYGIENE MEASURES

Not relevant

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Impregnated cloth, card or tissue
COLOUR	Colourless
ODOUR	Characteristic
BOILING POINT (°C)	>100 (>212 F)
RELATIVE DENSITY	1.000 @ 20 °C (68 F)
VAPOUR PRESSURE	2.33 kPa @ 20 °C (68 F)
pH-VALUE, CONC. SOLUTION	5-7
FLASH POINT (°C)	>55 (>131 F) CC (Closed cup).

10 STABILITY AND REACTIVITY

STABILITY

Stable under normal temperature conditions.

CONDITIONS TO AVOID

Not relevant.

11 TOXICOLOGICAL INFORMATION

INHALATION

No specific health warnings noted.

INGESTION

No specific health warnings noted.

SKIN CONTACT

No specific health warnings noted.

EYE CONTACT

No specific health warnings noted.

PC-CLENE TUB 100 WIPES

HEALTH WARNINGS No specific health warnings noted. No specific acute or chronic health impact noted, but this chemical may still have adverse impact on human health, either in general or on certain individuals with pre-existing or latent health problems.

OTHER HEALTH EFFECTS

This substance has no evidence of carcinogenic properties.

Name	1-METHOXY-2-PROPANOL
Toxic Dose 1 - LD 50	5200 mg/kg (oral rat)
Toxic Dose 2 - LD 50	11700 mg/kg (oral-mouse)

12 ECOLOGICAL INFORMATION

ECOTOXICITY

Not regarded as dangerous for the environment.

WATER HAZARD CLASSIFICATION

WGK 2

Name	1-METHOXY-2-PROPANOL
LC 50, 96 Hrs, Fish mg/l	20800
EC 50, 48 Hrs, Daphnia, mg/l	23300

13 DISPOSAL CONSIDERATIONS

DISPOSAL METHODS

No specific disposal method required.

14 TRANSPORT INFORMATION

	No transport warning sign required.
ROAD TRANSPORT NOTES	Not Classified
RAIL TRANSPORT NOTES	Not classified.
SEA TRANSPORT NOTES	Not classified.
AIR TRANSPORT NOTES	Not classified.
ENVIRONMENTALLY HAZARDOUS SUBSTANCE/MARINE POLLUTANT	No.
ADR CLASS	Not classified for transportation.

15 REGULATORY INFORMATION

RISK PHRASES

NC Not classified.

SAFETY PHRASES

NC Not classified.

UK REGULATORY REFERENCES

Chemicals (Hazard Information & Packaging) Regulations.

The Control of Substances Hazardous to Health Regulations 2002 (S.I 2002 No. 2677) with amendments.

EU DIRECTIVES

Dangerous Substance Directive 67/548/EEC.

Dangerous Preparations Directive 1999/45/EC.

System of specific information relating to Dangerous Preparations. 2001/58/EC.

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

PC-CLENE TUB 100 WIPES

Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 with amendments.

APPROVED CODE OF PRACTICE

Classification and Labelling of Substances and Preparations Dangerous for Supply.

GUIDANCE NOTES

Workplace Exposure Limits EH40.

16 OTHER INFORMATION

REVISION COMMENTS

Revised in accordance with CHIP3 and EU Directives 1999/45/EC and 2001/58/EC

ISSUED BY

Helen O'Reilly

REVISION DATE NOVEMBER 2009

REV. NO./REPL. SDS 5

GENERATED

SDS NO. 10638

RISK PHRASES IN FULL

R10 Flammable.

R67 Vapours may cause drowsiness and dizziness.

DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.