

LEDs & INDICATORS


503 A Series

- Press fit body for various panel thicknesses, panel cut-out 8mm diameter
- Stripped 10mm wire termination 280mm long and solder tags options as standard
- LED, Filament 6-28V 30-40mA and Neons 125-240V 0.8-1mA, as standard
- Neon-replacement LED version is fitted with resistor and operates at 240V AC. Operating life 50,000 hours
- Polycarbonate lens/body and brushed chrome bezel
- Body 25.4mm (1") long as standard, 16.7mm to order
- Maximum working temperature 105°C
- Red, green, amber lens colour options as standard
- Other lens colour options to order
- Two cylinder lens styles as standard, 6 other lens style options to order
- Custom wire lengths and specification to order
- Removable collar fits to rear of panel for improved retention




TYPE NO.	503 XX XX - XXXX - T / XXX
503 Series Indicator	503
Lens cylinder tapered sides	1
Lens cylinder curved sides	2
Lens cylinder straight sides	3
Lens domed	4
Lens arrow	5
Lens triangle	6
Lens square	7
Lens circle	8
Stripped wire 280mm long	05
Solder tag termination	11
LED, white cathode & black anode wires	LED
LED, neon-replacement, 240V 1mA	LED2
Filament 6V 40mA, white wire	640
Filament 14V 40mA, yellow wire	1440
Filament 24V 35mA, green wire	24
Filament 28V 30mA, green wire	28
Neon 125V 1mA, blue wire	125
Neon 240V 0.8mA, red wire	240
Transparent lens	T
Lens colour Red	RED
Lens colour Green	GRN
Lens colour Amber	AMB

Body Dimensions



Body 1 standard

Lens Options



lenses 1-2 standard



+44 (0)1638 716101
 info@camdenboss.com
 www.camdenboss.com

We operate a constant improvement policy,
 our products are subject to change without notice.

Ver 1.0 Iss2

CAMDENBOSS
 ELECTRONICS & ENCLOSURES

PCB
 TERMINAL
 BLOCKS

INTER-
 CONNECTION

FUSES &
 FUSE-
 HOLDERS

LEDs &
 INDICATORS

MINIATURE
 SWITCHES

LIMIT &
 SAFETY
 SWITCHES

CONTROL
 PRODUCTS

INTERFACE
 MODULES &
 SUPPORTS

RELAY
 BASES

ENCLOSURES

BATTERIES

TRANS-
 FORMERS