

Material Safety Data Sheet

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Trade name or designation of the mixture 400

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Metal alloy for soft solder

Uses advised against Not available.

1.3. Details of the supplier of the safety data sheet

Company name : Premier Farnell

Address : 150 Armley Road

Leeds LS12 2QQ

Tel. : +44 (0) 870 129 8608

Emergency Contacts : +44 (0) 870 202530

Section 2: Hazards identification

2.1. Classification of the substance or mixture

The mixture has been assessed and/or tested for its physical, health and environmental hazards and the following classification applies.

Classification according to Directive 67/548/EEC or 1999/45/EC as amended

This preparation does not meet the criteria for classification according to Directive 1999/45/EC as amended.

Remark: The classification for this article has been derived with the use of the regulations for mixtures.

Hazard summary

Physical hazards Not classified for physical hazards.

Health hazards Not classified for health hazards. However, occupational exposure to the mixture or substance(s) may cause adverse health effects.

Environmental hazards Not classified for hazards to the environment.

Specific hazards Not available.

Main symptoms Not available.

2.2. Label elements

Label according to Directive 67/548/EEC or 1999/45/EC as amended

EC number -

EC label Not available.

R-phrases Not available.

S-phrases Not available.

Authorisation number Not available.

Supplemental label information Not applicable.

2.3. Other hazards

Remark: As an article, this product has not to be labelled pursuant to current EU-regulation.

Material Safety Data Sheet

Section 3: Composition/information on ingredients

3.1. Mixtures

General information

Chemical name	%	CAS-No. / EC No.	Reach Registration No.	Index No.	Notes
tin Classification: DSD: - CLP: -	96.5 - 99.5	7440-31-5 231-141-8	-	-	#
Copper Metal Classification: DSD: - CLP: -	0.5 - 3.5	7440-50-8 231-159-6	-	-	

PBT: persistent, bioaccumulative and toxic substance.

vPvB: very persistent and very bioaccumulative substance.

#: This substance has been assigned Community workplace exposure limit(s).

Composition comments The full text for all R-phrases is displayed in Section 16.

Section 4: First aid measures

General information Not available.

4.1. Description of first aid measures

Inhalation	Move to fresh air. Call a physician if symptoms develop or persist.
Skin contact	Rinse skin with water/shower. Get medical attention if irritation develops and persists. For hot product: Immediately immerse in or flush affected area with large amounts of cold water to dissipate heat. Cover with clean cotton sheeting or gauze and get prompt medical attention.
Eye contact	Remove contact lenses, if present and easy to do. Rinse immediately with plenty of water, also under the eyelids. Get medical attention if irritation develops and persists.
Ingestion	Rinse mouth. Get medical advice/attention if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed Not available.

4.3. Indication of any immediate medical attention and special treatment needed Treat symptomatically. Symptoms may be delayed.

Section 5: Firefighting measures

General fire hazards Not available.

5.1. Extinguishing media

Suitable extinguishing media	Use fire-extinguishing media appropriate for surrounding materials.
Unsuitable extinguishing media	Water, CO2 or Foam

5.2. Special hazards arising from the substance or mixture The product itself does not burn. Hot melt

Material Safety Data Sheet

5.3. Advice for firefighters

Special protective equipment for firefighters Firefighters should wear full protective clothing including self contained breathing apparatus.

Special fire fighting procedures Water runoff can cause environmental damage.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel Keep unnecessary personnel away. Ensure adequate ventilation. Wear appropriate protective equipment and clothing during clean-up.

For emergency responders Not available.

6.2. Environmental precautions

Contact local authorities in case of spillage to drain/aquatic environment. Avoid discharge into drains, water courses or onto the ground.

6.3. Methods and material for containment and cleaning up

Remove material, as much as possible, using mechanical equipment. Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal. For waste disposal, see section 13.

6.4. Reference to other sections

For personal protection, see section 8. For waste disposal, see section 13.

Section 7: Handling and storage

7.1. Precautions for safe handling

Use only with adequate ventilation. Avoid inhalation of vapours and aerosol spray. Do not get this material in contact with eyes. Avoid contact with skin. Avoid prolonged exposure. Avoid release to the environment. Use care in handling/storage.

7.2. Conditions for safe storage, including any incompatibilities

Store in a dry place. Use care in handling/storage. Store in accordance with local/regional/national/international regulation.

7.3. Specific end use(s)

Not available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limits

UK. EH40 Workplace Exposure Limits (WELs)

Components	Type	Value	Form
Copper Metal (7440-50-8)	STEL	2mg/m ³	Inhalable dusts and mists.
	TWA	1mg/m ³	Inhalable dusts and mists.
		0.2mg/m ³	Fume.

EU. Indicative Exposure Limit Values in Directives 91/322/EEC, 2000/39/EC, 2006/15/EC, 2009/161/EU

Components	Type	Value
TIN (7440-31-5)	TWA	2mg/m ³

Material Safety Data Sheet

Biological limit values Recommended monitoring procedures

No biological exposure limits noted for the ingredient(s).
Follow standard monitoring procedures.

8.2. Exposure controls

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Provide adequate general and local exhaust ventilation.

Individual protection measures, such as personal protective equipment

Eye/face protection

Chemical goggles are recommended.

Skin protection

- Hand protection

- Other

Use protective gloves made of: Leather

Personal protection equipment should be chosen according to the CEN standards and in discussion with the supplier of the personal protective equipment. Normal work clothing (long sleeved shirts and long pants) is recommended.

Respiratory protection

When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.

Thermal hazards

Thermally protective gloves are recommended. If contact with forearms is likely, wear gauntlet-style gloves. Avoid contact with molten material.

Hygiene measures

Avoid contact with skin. When using, do not eat, drink or smoke. Handle in accordance with good industrial hygiene and safety practices. Avoid contact with eyes.

Environmental exposure controls

Not available.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance

Physical state

Solid.

Form

Roll.

Colour

Metallic.

Odour

Odourless.

Odour threshold

Not available.

pH

Not applicable.

Melting point/freezing point

227°C - 310°C (440.6°F - 590°F)

Initial boiling point and boiling range

Not available.

Flash point

Not applicable.

Evaporation rate

Not applicable.

Flammability (solid, gas)

Not applicable.

Upper/lower flammability or explosive limits

Flammability limit - lower (%)

Not available.

Flammability limit - upper (%)

Not available.

Vapour pressure

Not applicable.

Vapour density

Not applicable.

Relative density

Not available.

Solubility(ies)

insoluble

Material Safety Data Sheet

Partition coefficient (n-octanol/water) Not available.
Decomposition temperature Not available.
Viscosity Not applicable.
Explosive properties Not available.
Oxidizing properties Not available.

9.2. Other information

Density 7 - 9g/ml @ 20°C

Section 10: Stability and reactivity

10.1. Reactivity Strong oxidizing agents.
10.2. Chemical stability Material is stable under normal conditions.
10.3. Possibility of hazardous reactions No dangerous reaction known under conditions of normal use.
10.4. Conditions to avoid None under normal conditions.
10.5. Incompatible materials Acids. Chlorine.
10.6. Hazardous decomposition products Not available.

Section 11: Toxicological information

General information Not available.

Information on likely routes of exposure

Ingestion Not available.
Inhalation Not available.
Skin contact Not available.
Eye contact Not available.
Symptoms Not available.

11.1. Information on toxicological effects

Components	Species	Test results
Copper Metal (7440-50-8) Acute Dermal LD50	Rat	> 2000 mg/kg, OECD Guideline 402
Oral LD50	Rat	> 2500 mg/kg, OECD Guideline 401

Skin corrosion/irritation Not available.
Serious eye damage/irritation Not available.
Respiratory sensitisation Not available.
Skin sensitisation Not available.
Germ cell mutagenicity Not available.
Carcinogenicity Not available.
Reproductive toxicity Not available.
Specific target organ toxicity - single exposure Not available.
Specific target organ toxicity -repeated exposure Not available.
Aspiration hazard Not available.
Mixture versus substance information Not available.
Other information Not available.

Section 12: Ecological information

12.1. Toxicity	Not expected to be harmful to aquatic organisms. Avoid discharge into drains, water courses or onto the ground.
12.2. Persistence and degradability	No data is available on the degradability of this product.
12.3. Bioaccumulative potential	Not available.
Bioconcentration factor (BCF)	Not available.
12.4. Mobility in soil	Not available.
12.5. Results of PBT and vPvB assessment	Not a PBT or vPvB substance or mixture.
12.6. Other adverse effects	Not available.

Section 13: Disposal considerations

13.1. Waste treatment methods	
Residual waste	Dispose of in accordance with local regulations.
Contaminated packaging	Empty containers should be taken to an approved waste handling site for recycling or disposal.
EU waste code	The Waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Disposal methods/information	Collect and reclaim or dispose in sealed containers at licensed waste disposal site.

Section 14: Transport information

ADR	Not regulated as dangerous goods.
IATA	Not regulated as dangerous goods.
IMDG	Not regulated as dangerous goods.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU regulations

Regulation (EC) No. 1005/2009 on substances that deplete the ozone layer, Annex I	Not listed.
Regulation (EC) No. 1005/2009 on substances that deplete the ozone layer, Annex II	Not listed.
Regulation (EC) No. 850/2004 on persistent organic pollutants, Annex I as amended	Not listed.
Regulation (EC) No. 689/2008 concerning the export and import of dangerous chemicals, Annex I, part 1 as amended	Not listed.
Regulation (EC) No. 689/2008 concerning the export and import of dangerous chemicals, Annex I, part 2 as amended	Not listed.
Regulation (EC) No. 689/2008 concerning the export and import of dangerous chemicals, Annex I, part 3 as amended	Not listed.
Regulation (EC) No. 689/2008 concerning the export and import of dangerous chemicals, Annex V as amended	Not listed.

Material Safety Data Sheet

Regulation (EC) No. 166/2006 Annex II Pollutant Release and Transfer Registry

Not listed.

Regulation (EC) No. 1907/2006, REACH Article 59(1) Candidate List as currently published by ECHA

Not listed.

Authorisations

Regulation (EC) No. 143/2011 Annex XIV Substances Subject to Authorisation

Not listed.

Restrictions on use

Regulation (EC) No. 1907/2006, REACH Annex XVII Substances subject to restriction on marketing and use as amended

Not listed.

Directive 2004/37/EC: on the protection of workers from the risks related to exposure to carcinogens and mutagens at work

Not regulated.

Directive 92/85/EEC: on the safety and health of pregnant workers and workers who have recently given birth or are breast feeding

Not regulated.

Other EU regulations

Directive 96/82/EC (Seveso II) on the control of major-accident hazards involving dangerous substances

Not regulated.

Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work

Not regulated.

Directive 94/33/EC on the protection of young people at work

Not regulated.

Other regulations

The product is classified and labelled in accordance with EC directives or respective national laws. This Safety Data Sheet complies with the requirements of Regulation (EC) No 1907/2006. The product does not need to be labelled in accordance with EC directives or respective national laws.

National regulations

Not available.

15.2. Chemical safety assessment

No Chemical Safety Assessment has been carried out.

Section 16: Other information

List of abbreviations Not available.

References Not available.

Information on evaluation method leading to the classification of mixture Not available.

Full text of any statements or R-phrases and H-statements under Sections 2 to 15 None.

Training information Not available.

Disclaimer The information in the sheet was written based on the best knowledge and experience currently available.

Part Number
507-1422