



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
B	ECN 4087: CN RELEASE	7/12/09	B. ZHANG
C	ECN 4168: ADDED L-COM LOGO BOTH SIDES	8/4/09	D. CASTRO
D	ECN 6638: UPDATED FORMAT, PACKAGING, AND LOGOS	1/31/13	D. DESJARDIN



UL 20276  
 (6) 30AWG COAXIAL LINES, BRAIDED SHIELD;  
 (1) 28AWG TWISTED PAIR, AL/MYLAR SHIELD;  
 (2) 30AWG TWISTED PAIR, AL/MYLAR SHIELD, W/DRAIN WIRE;  
 (1) 28AWG TWISTED PAIR,  
 (2) 30AWG TWISTED PAIR, AL/MYLAR SHIELD, W/DRAIN WIRE;  
 (1) 22AWG TWISTED PAIR,  
 (1) 24AWG TWISTED PAIR,  
 (6) 28AWG SINGLE CONDUCTOR,  
 OVERALL SHIELD: AL/MYLAR AND BRAID,  
 OUTER JACKET: PVC, GRAY (PANTONE 424C)

MODEL NUMBER	LENGTH	
	FEET	METERS
CTLEVCMM-3	3.0	0.91
CTLEVCMM-5	5.0	1.52
CTLEVCMM-10	10.0	3.05
CTLEVCMM-15	15.0	4.57
CTLEVCMM-25	25.0	7.62
CTLEVCMM-50	50.0	15.24

**NOTES:**

1. PINS 8, 18 AND 28 RECESSED TO PROVIDE PROPER POWER/GROUND SEQUENCING
2. CABLES TO BE TESTED FOR CONTINUITY
3. CABLES SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $>12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $>60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $>120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $>300$ [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	APPROVALS DRAWN BY Bill_Zhang CHECKED BY Frank_Mao APPROVED BY Frank_Mao	DATE 05/22/09 06/12/09 06/12/09	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	
COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>CTLEVCMM</b>
REF	SCALE: NONE	CAD FILE: CTLEVCMM.SLDDRW	REV. <b>D</b> SHEET 1 OF 1