



SAFETY DATA SHEET 5W30 SEMI SYNTHETIC

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name 5W30 SEMI SYNTHETIC
Product No. DRG001, DRG005, DRG025, DRG199, GFV010, GFV025, GFV050, GFV199, MAC320, XAH010, XAH050, MAC937, YAH199, YAH025, JSB122, JSB107, JSB108, MOR124, NRE001, NRE004, XAH455, XRE001, XRE004, HBS103, YAH020, NRE002, HBS104, QOL124

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Engine oil.

1.3. Details of the supplier of the safety data sheet

Supplier TETROSYL LIMITED
BEVIS GREEN WORKS
WALMERSLEY
BURY
BL9 6RE
0161 764 5981
0161 797 5899
info@tetrosyl.com
Manufacturer TETROSYL LIMITED
BEVIS GREEN WORKS
WALMERSLEY
BURY
BL9 6RE
0161 764 5981
0161 797 5899
info@tetrosyl.com

1.4. Emergency telephone number

0161 764 5981

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical and Chemical Hazards	Not classified.
Human health	Not classified.
Environment	Not classified.

Classification (1999/45/EEC) Not classified.

The Full Text for all R-Phrases and Hazard Statements are Displaved in Section 16.

2.2. Label elements

5W30 SEMI SYNTHETIC

Label In Accordance With (EC) No. 1272/2008

No pictogram required.

Precautionary Statements

P101	If medical advice is needed, have product container or label at hand.
P102	Keep out of reach of children.

2.3. Other hazards**SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS****3.2. Mixtures**

ORGANOMOLYBDENUM AMIDE	0.1 - <0.3%
CAS-No.: 445409-27-8	EC No.:
Classification (EC 1272/2008) Aquatic Chronic 2 - H411	Classification (67/548/EEC) N;R51/53.
ZINC DIALKYL DITHIOPHOSPHATE	0.5 - < 1.0%
CAS-No.: 68649-42-3	EC No.: 272-028-3
Classification (EC 1272/2008) Skin Irrit. 2 - H315 Eye Dam. 1 - H318 Aquatic Chronic 2 - H411	Classification (67/548/EEC) Xi;R38,R41. N;R51/53.

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

SECTION 4: FIRST AID MEASURES**4.1. Description of first aid measures****General information**

Get medical attention if any discomfort continues. Remove affected person from source of contamination.

General first aid, rest, warmth and fresh air.

Inhalation

In case of inhalation of spray mist: Move person into fresh air and keep at rest.

Ingestion

Contact physician if larger quantity has been consumed. Rinse mouth thoroughly.

Skin contact

Promptly wash contaminated skin with soap or mild detergent and water. Promptly remove clothing if soaked through and wash as above. Contact physician if irritation continues or sores develop.

Eye contact

Immediately flush with plenty of water for up to 15 minutes. Remove any contact lenses and open eyes wide apart. Do not rub eye.

4.2. Most important symptoms and effects, both acute and delayed**General information**

The severity of the symptoms described will vary dependant of the concentration and the length of exposure.

NOTE! Effects may be delayed. Keep affected person under observation.

5W30 SEMI SYNTHETIC**Inhalation**

May cause an asthma-like shortness of breath. Vapours may cause headache, fatigue, dizziness and nausea.

Ingestion

May cause discomfort if swallowed. May cause stomach pain or vomiting. May cause nausea, headache, dizziness and intoxication.

Skin contact

Prolonged or repeated contact with skin may cause redness, itching, irritation and eczema/chapping. Allergic rash.

Eye contact

May cause temporary eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

No recommendation given, but first aid may still be required in case of accidental exposure, inhalation or ingestion of this chemical. If in doubt, GET MEDICAL ATTENTION PROMPTLY!

SECTION 5: FIREFIGHTING MEASURES**5.1. Extinguishing media****Extinguishing media**

Use: Foam, carbon dioxide or dry powder. Use fire-extinguishing media appropriate for surrounding materials.

Unsuitable extinguishing media

Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture**Hazardous combustion products**

During fire, toxic gases (CO, CO₂) are formed.

Unusual Fire & Explosion Hazards

No unusual fire or explosion hazards noted.

Specific hazards

Fire creates: Carbon monoxide (CO). Carbon dioxide (CO₂).

5.3. Advice for firefighters

Protective equipment for fire-fighters

Leave danger zone immediately.

SECTION 6: ACCIDENTAL RELEASE MEASURES**6.1. Personal precautions, protective equipment and emergency procedures**

Follow precautions for safe handling described in this safety data sheet. Avoid inhalation of vapours and aerosol spray. Avoid contact with eyes and prolonged skin contact. Provide adequate ventilation. In case of spills, beware of slippery floors and surfaces.

6.2. Environmental precautions

Avoid discharge into drains, water courses or onto the ground. The product should not be dumped in nature but collected and delivered according to agreement with the local authorities.

6.3. Methods and material for containment and cleaning up

Stop leak if possible without risk. Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Provide ventilation and confine spill. Do not allow runoff to sewer. Collect with absorbent, non-combustible material into suitable containers.

6.4. Reference to other sections

Wear protective clothing as described in Section 8 of this safety data sheet. Collect and dispose of spillage as indicated in section 13.

SECTION 7: HANDLING AND STORAGE

5W30 SEMI SYNTHETIC**7.1. Precautions for safe handling**

Good personal hygiene is necessary. Wash hands and contaminated areas with water and soap before leaving the work site. Do not eat, drink or smoke when using the product. Avoid forming spray/aerosol mists. Provide good ventilation. Avoid contact with skin and eyes. Always remove oil with soap and water or skin cleaning agent, never use organic solvents. Do not use oil-contaminated clothing or shoes, and do not put rags moistened with oil into pockets.

7.2. Conditions for safe storage, including any incompatibilities

Keep upright. Store in tightly closed original container.

7.3. Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION**8.1. Control parameters****8.2. Exposure controls**

Protective equipment



Engineering measures

Provide adequate ventilation. Observe Occupational Exposure Limits and minimise the risk of inhalation of vapours.

Respiratory equipment

No specific recommendations.

Hand protection

Protective gloves should be used if there is a risk of direct contact or splash. Nitrile gloves are recommended, but be aware that the liquid may penetrate the gloves. Frequent change is advisable.

Eye protection

Wear approved, tight fitting safety glasses where splashing is probable.

Other Protection

Wear suitable protective clothing as protection against splashing or contamination.

Hygiene measures

Wash contaminated clothing before reuse. Wash promptly with soap & water if skin becomes contaminated.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES**9.1. Information on basic physical and chemical properties**

Appearance	Liquid
Colour	Brown.
Odour	Oil smell.
Solubility	Insoluble in water
Initial boiling point and boiling range (°C)	>250°C
Melting point (°C)	Not determined.
Relative density	0.860
Vapour density (air=1)	Not determined.

5W30 SEMI SYNTHETIC

Vapour pressure
Not determined.
Evaporation rate
Not determined.
Viscosity 55 cSt 40°C
Decomposition temperature (°C)
Not determined.
Odour Threshold, Lower
Not determined.
Odour Threshold, Upper
Not determined.
Flash point (°C) 205°C
Auto Ignition Temperature (°C)
Not determined.
Flammability Limit - Lower(%)
Not determined.
Flammability Limit - Upper(%)
Not determined.
Partition Coefficient Not determined.
(N-Octanol/Water) >4 (estimate)
Oxidising properties
Not available.

9.2. Other information

None.

SECTION 10: STABILITY AND REACTIVITY**10.1. Reactivity**

No specific reactivity hazards associated with this product.

10.2. Chemical stability

No particular stability concerns.

10.3. Possibility of hazardous reactions

Not applicable.

10.4. Conditions to avoid

No specific conditions are likely to result in a hazardous situation.

10.5. Incompatible materials

Materials To Avoid

No incompatible groups noted.

10.6. Hazardous decomposition products

None under normal conditions.

SECTION 11: TOXICOLOGICAL INFORMATION**11.1. Information on toxicological effects**

Toxic Dose 1 - LD 50

>2000 (Lubricating oils, (petroleum), C20-50, hydrotreated neutral oil-based) mg/kg (oral rat)

SECTION 12: ECOLOGICAL INFORMATION

5W30 SEMI SYNTHETIC**Ecotoxicity**

The product components are not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

12.1. Toxicity

LC 50, 96 Hrs, Fish mg/l 100 (estimate) (Lubricating oils, (petroleum), C20-50, hydrotreated neutral oil-based)

12.2. Persistence and degradability**Degradability**

There are no data on the degradability of this product.

12.3. Bioaccumulative potential**Bioaccumulative potential**

No data available on bioaccumulation.

Partition coefficient

Not determined. >4 (estimate)

12.4. Mobility in soil**Adsorption/Desorption Coefficient**

Not available.

12.5. Results of PBT and vPvB assessment

Not Classified as PBT/vPvB by current EU criteria.

12.6. Other adverse effects

Not available.

SECTION 13: DISPOSAL CONSIDERATIONS**General information**

Waste is classified as hazardous waste. Disposal to licensed waste disposal site in accordance with the local Waste Disposal Authority.

13.1. Waste treatment methods

Confirm disposal procedures with environmental engineer and local regulations.

SECTION 14: TRANSPORT INFORMATION**General**

The product is not covered by international regulation on the transport of dangerous goods (IMDG, IATA, ADR/RID).

14.1. UN number**14.2. UN proper shipping name****14.3. Transport hazard class(es)****Transport Labels**

No transport warning sign required.

14.4. Packing group**14.5. Environmental hazards**

Environmentally Hazardous Substance/Marine Pollutant
No.

5W30 SEMI SYNTHETIC**14.6. Special precautions for user****14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code**

Not applicable.

SECTION 15: REGULATORY INFORMATION**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

EU Legislation

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments. Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 with amendments.

15.2. Chemical Safety Assessment

No chemical safety assessment has been carried out.

SECTION 16: OTHER INFORMATION

Revision Comments

NOTE: Lines within the margin indicate significant changes from the previous revision.

Revision Date	07/01/2014
Revision	19
Supersedes date	30/10/2012 V18
Safety Data Sheet Status	Approved.

Risk Phrases In Full

R38	Irritating to skin.
NC	Not classified.
R41	Risk of serious damage to eyes.
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Hazard Statements In Full

H318	Causes serious eye damage.
H315	Causes skin irritation.
H411	Toxic to aquatic life with long lasting effects.