

Fig. 750 Series/Technical data see page 24/Delivered without miniature WSB markers
750/753 Series marking see pages 10 ... 11 / 12 ... 13


The interface integrated in the I/O module allows the connection of any device which is equipped with an RS-232 C interface.

The RS-232 C interface guarantees high interference immunity because of the electrically isolated signals.

The interface operates in accordance with the TIA/EIA-F, CCITT V.28/DIN 66259-1 standard.

The shield (screen) is directly connected to the DIN rail.

The connected device can communicate directly with the control unit via the fieldbus coupler. The active communication channel works independently of the higher-level fieldbus system and allows full duplex operation up to 19200 baud.



Description	Item No.	Pack. Unit
RS-232 C / 9600 / N / 8 / 1	750-650	1
RS-232 C / 9600 / N / 8 / 1 / 5 bytes	750-650/000-001	1
RS-232 C / 9600 / E / 7 / 2	750-650/000-002	1
RS-232 C / 4800 / E / 7 / 1	750-650/000-004	1
RS-232 C / 9600 / E / 8 / 1	750-650/000-006	1
RS-232 C / 2400 / E / 8 / 1	750-650/000-009	1
RS-232 C / 19200 / N / 8 / 1	750-650/000-010	1
RS-232 C / 19200 / E / 8 / 1	750-650/000-011	1
RS-232 C / 2400 / N / 8 / 1	750-650/000-012	1
RS-232 C / 4800 / E / 7 / 2	750-650/000-013	1
RS-232 C / 4800 / E / 8 / 1	750-650/000-015	1
RS-232 C / Configurable	750-650/003-000	1
RS-232 C Interface (without connector)	753-650	1
RS-232 C / Configurable (without connector)	753-650/003-000	1
Accessories		
753 Series Connectors	753-110	25
Coding elements	753-150	100
Miniature WSB Quick marking system		
plain	248-501	5
with marking	see pages 352 ... 353	
Approvals		
Conformity marking	Also see "Approvals Overview" in Section 1	
Shipbuilding (versions upon request)	CE ABS, BV, DNV, GL, KR, LR*, NKK*, PRS*, RINA* *753 Series, pending	
UL 508		
ANSI/ISA 12.12.01	Class I, Div. 2, Grp. ABCD, T4	
EN 60079-0, -15	I M2 / II 3 GD Ex nA IIC T4	
EN 61241-0, -1		

Technical Data	
Transmission channels	1 TxD / 1 RxD, full duplex
Baud rate	9600 baud (factory preset) 1200 ... 19200 baud 57600 baud (750-650/003-000)
Bit skew	< 3 %
RS-232 line length (max.)	15 m
Buffer	128 bytes in/16 bytes out
Max. current consumption (internal)	55 mA
Power supply	via system voltage DC/DC
Isolation	500 V system/supply
Internal bit width	1 x 24 bits in/out (3 bytes user data) 1 x 8 bits control/status
Wire connection	CAGE CLAMP®
Cross sections	0.08 mm² ... 2.5 mm² / AWG 28 ... 14
Stripped lengths, 750/753 Series	8 ... 9 mm / 0.33 in 9 ... 10 mm / 0.37 in
Width	12 mm
Weight	51.5 g
EMC: CE - immunity to interference	acc. to EN 61000-6-2 (2005)
EMC: CE - emission of interference	acc. to EN 61000-6-4 (2007)
EMC: marine applications	
- immunity to interference	acc. to Germanischer Lloyd (2003)
EMC: marine applications	
- emission of interference	acc. to Germanischer Lloyd (2003)