


WS60/WS120

Portable Bench Scale



- Low cost, 1 part in 3000 scale
- Capacity 60 kg x 20 g or 120 kg x 50 g
- Stainless steel platform top
- Large platform size
- Stainless steel display pod
- Bench or wall mounted display pod
- Mains or battery power
- Low profile platform

WS60/WS120 Portable Bench Scale

Features

WS60 and WS120 bench scales offer the user a competitively priced bench scale with 1:3000 resolution - giving 60 kg x 20 g or 120 kg x 50 g performance, incorporating four full load bridge load cells, with self-levelling feet.

The tough low profile platform has a brushed stainless steel top for ease of cleaning and a generous platform size. It is mounted on four anti-slip rubber feet.

800 mm of cable connects the platform to the brushed stainless steel display pod which features clear 17 mm high LCD digits. A plastic display pod bracket is included to allow the display to be wall or bench mounted.

Key display features are on/off; push button tare to enable weights of empty containers to be removed and net weight only displayed; kg / lb switching to give readings in either metric or imperial measures and hold which allows the weight to be frozen, even when the package is removed.

The scale also features auto zero tracking to automatically compensate for small fluctuations in zero such as a build up of material on the platform.

To extend battery life an auto-off feature is standard, with the scale switching itself off after 2 minutes of inactivity.

Specifications

Capacity -

WS60: 60 kg x 20 g/130 lb x 0.05 lb
WS120: 120 kg x 50 g/260 lb x 0.1 lb

Self-Levelling Feet

Power - 4 x 1.5 volt AAA batteries (not supplied)
6 volt UK/EU power adaptor (supplied)

Platform Size - 380 mm x 300 mm x 27 mm high

Display Pod Size - 158 mm x 80 mm x 27 mm

Display - 5¹/₂ digit, 17 mm high, LCD

Function Keys - On/off; tare; kg/lb; hold

Annunciators - Zero; net; hold; kg/lb

Tare - 100% subtractive


Operating Temperature - +5° C to +40° C

Approvals - CE
WEEE directive

Unit Weight - 3.9 kg

Packing Dimensions - 450 mm x 400 mm x 60 mm

Packed Weight - 5 kg



a division of Avery Weigh-Tronix

Salter Brecknell Weighing Products

P.O. Box 9533, Smethwick, West Midlands, B66 2TE

Tel: 0870 444 6132 Fax: 0870 010 2241

E-mail: sales@salterbrecknell.co.uk

www.salterbrecknell.co.uk

